

# PHILIPS

Motorcycle  
headlights

X-tremeVision Moto

Type of lamp: H4

Pack of: 1

12V, 60/55W

More light



12342XV+BW



## Feel safe, ride safe

Up to 130% more brightness

For maximum performance and safety, Philips X-tremeVision moto bulbs are engineered with state-of-the-art technology to offer up to 130% more brightness for riders who need to see farther.

### Up to 130% more brightness on the road

- Up to 130% brighter light on the road

### Optimised design for better performance

- Optimised lifetime and durability

### Maximum brightness on the road

- Boost your moto's light projection on the road

### High-quality and ultra-resistant headlamp

- Philips moto lamps are made of high-quality quartz glass
- Respecting the high quality standards of ECE homologation
- The favoured choice of major motorcycle manufacturers

# Highlights

## Up to 130% more brightness

Thanks to improved filament geometry and the use of unique gas compositions the X-tremeVision moto headlamps project up to 130% brighter light on the road.

## Good lifetime and durability

Philips X-tremeVision moto bulbs are designed with state-of-the-art technology. The bulbs are filled with a unique gas composition that reduces the deterioration of the lamp's filament, which improves its durability and therefore optimises the lamp's lifetime.

## Boost the light on the road

Based on state-of-the-art technology in filament design and optimised geometry, X-tremeVision moto lamps are engineered for high performance. The bright white light is projected where it matters the most on the road ahead of you. This will help you to see farther and to react faster if someone from the side steps or drives suddenly into your lane.

## High-quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of

explosion. So Philips quartz-glass lamps (filament 2 650°C and glass 800°C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light. And more powerful light means an enhanced driving experience, however dark the road in front of you.

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality materials and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Manufacturers' choice

For over 100 years, Philips bulbs have been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard in modern vehicles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

# Specifications

## Packaging Data

EAN1: 8719018000569  
EAN3: 8719018000576  
Packaging type: BW

## Light characteristics

Colour temperature: Up to 3500 K

## Marketing specifications

Expected benefits: More light

## Product description

Range: X-tremeVision Moto  
Technology: Halogen  
Application: High beam, Low beam  
Type: H4  
Homologation ECE  
Base: P43t-38  
Designation: 12342XV+BW

## Electrical characteristics

Voltage: 12 V  
Wattage: 60/55 W

## Ordering information

Ordering code: 00056930  
Order entry: 12342XV+BW

## Packed product information

MOQ (for professionals): 10  
Pack Quantity: 1  
Gross weight per piece [g]: 34.4  
Height [cm]: 12.9  
Length [cm]: 9.5  
Net weight per piece [g]: 22  
Width [cm]: 4.9

## Outer pack information

Gross weight per piece [kg]: 0.462  
Height [cm]: 13  
Length [cm]: 25.5  
Width [cm]: 19

