



Philips EnergySaver
Linear Compact
Fluorescent

7W

PL-S
G23; 2-Pin Base

046677230227

Energy savings and long life

Features ALTO technology.

Philips Compact Fluorescent light bulbs offer significant energy savings, great light output and a wide variety of shapes and sizes.

Ease of use

- Designed for use with magnetic ballasts

Light effect

- Provides a comfortable and relaxing environment

Perfect Shape

- For use in recessed and surface mounted downlight fixtures

Sustainable choice

- Reduced mercury for an environmentally friendly alternative

PHILIPS

Linear Compact Fluorescent
7W PL-S, G23; 2-Pin Base

Specifications

Technical specifications

- Lamp holder: PL-S
- Placement: Recessed can
- Indoor

- Number of lamps: 1
- Wattage: 7 W

Light characteristics

- Application: Comfortable light, Soft light

046677230227

Highlights

ALTO Lamp Technology

Reduced mercury for an environmentally friendly alternative

For use with existing ballasts

Designed for use with magnetic ballasts

For general lighting use

For use in recessed and surface mounted downlight fixtures

Soft white light

Provides a comfortable and relaxing environment



Issue date 2017-02-02

Version: 2.0.0

12 NC: 9278 665 82700
UPC: 0 46677 23022 7

© 2017 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* This lamp is better for the environment because of its reduced mercury content. All Philips ALTO lamps give you end-of-life options, which can simplify and reduce your lamp disposal costs, depending on your state and local regulations.