



Philips EnergySaver  
Linear Compact  
Fluorescent

9W

PL-S  
G23; 2-Pin Base

046677230326

## Energy savings and long life

Features ALTO technology.

Philips Compact Fluorescent light bulbs offer significant energy savings, great light output and a wide variety of shapes and sizes.

### **Ease of use**

- Designed for use with magnetic ballasts

### **Light effect**

- Provides a comfortable and relaxing environment

### **Perfect Shape**

- For use in recessed and surface mounted downlight fixtures

### **Sustainable choice**

- Reduced mercury for an environmentally friendly alternative

# PHILIPS

Linear Compact Fluorescent  
9W PL-S, G23; 2-Pin Base

# Specifications

## Technical specifications

- Lamp holder: PL-S
- Placement: Recessed can
- Indoor

- Number of lamps: 1
- Wattage: 9 W

## Light characteristics

- Application: Comfortable light, Soft light

046677230326

# Highlights

## ALTO Lamp Technology

Reduced mercury for an environmentally friendly alternative

## For use with existing ballasts

Designed for use with magnetic ballasts

## For general lighting use

For use in recessed and surface mounted downlight fixtures

## Soft white light

Provides a comfortable and relaxing environment



Issue date 2017-02-02

Version: 2.0.0

12 NC: 9278 670 82700  
UPC: 0 46677 23032 6

© 2017 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* This lamp is better for the environment because of its reduced mercury content. All Philips ALTO lamps give you end-of-life options, which can simplify and reduce your lamp disposal costs, depending on your state and local regulations.