



Philips
Heat Lamp

250W

BR40
Medium Base

046677416744



Light for all of your specialized fixtures

Philips Specialty Incandescent and halogen bulbs provide the perfect light for accent and display lighting as well as general lighting in a variety of applications.

Use in any room in your home

- Provides a comfortable warmth using infrared technology

Perfect Shape

- Ideal for recessed cans and track light fixtures

PHILIPS

Heat Lamp
250W BR40, Medium Base

046677416744

Specifications

Technical specifications

- Indoor
- Lamp holder: BR40
- Number of lamps: 1
- Placement: Recessed cans, Track light

- Power supply: 120 V
- Wattage: 250 W

Light characteristics

- Application: Special application

Highlights

Ideal for Bathrooms

Provides a comfortable warmth using infrared technology

Use in indoor flood fixtures

Ideal for recessed cans and track light fixtures



Issue date 2016-09-18

Version: 1.0.0

12 NC: 9252 551 36300
UPC: 0 46677 41674 4

© 2016 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com