



Philips Halogen
Reflector - Flood

83w (120w)
Medium base (E26)
Sparkling light

046677424985

Energy savings without sacrifice

A bright alternative to incandescents

Philips 83W dimmable halogen indoor/outdoor flood provides bright ambient light. An energy saving alternative to 120W incandescents, it has no mercury, can last up to 4 years* and has an estimated yearly energy cost of \$10.00**

Energy efficiency

- Reduces energy costs
- Meets efficiency standards

Bright white light

- Bright alternative to incandescent

Easy to use

- Instant on
- Dimmable

PHILIPS

Reflector - Flood
83w (120w) Medium base (E26), Sparkling light

Specifications

Bulb characteristics

- Shape: Reflector Flood
- Lamp shape code: PAR38
- Base: Medium Screw (E26)
- Voltage: 120 V
- Dimmable

Power consumption

- Wattage: 83 W
- Wattage equivalent: 120 W

Light characteristics

- Application: Accent light

- Color rendering index (CRI): 100
- Color temperature: 2730 K
- Light output: 1750 lumen
- Light effect/finish: Clear

Durability

- Average life (at 2.7 hrs/day): 4 year(s)
- Lifetime of lamps: 4400 hour(s)

Bulb dimensions

- Height: 5.44 inch
- Width: 4.31 inch

046677424985

Highlights

Instant on



INSTANT ON

Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

Alternative to incandescent

This halogen light bulb provides a bright, white light that is ideal for creating a refreshing atmosphere in your home.

Dimmable

This bulb can be used with most dimmers to create your desired ambience.

Meets efficiency standards

This bulb meets Federal minimum efficiency standards.

Reduces energy costs

This bulb saves up to 31%*** in electricity costs when compared to a 120W incandescent



Issue date 2018-06-10

Version: 7.0.1

12 NC: 9257 133 36301

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

***Compared to a 120 watt Halogen PAR38 rated at 1740 lumens, this 83 watt PAR38 provides 1750 lumens and saves 31% energy.

*Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use.

**Compared to a 120 watt Halogen PAR38 rated at 1740 lumens, this 83 watt PAR38 provides 1750 lumens and saves 31% energy.