



Philips LED
Reflector

8-7-3W (65W)

Medium Screw base
SceneSwitch
Non-dimmable

046677473662



One bulb, 3 color settings

Works with your existing switch

With Philips SceneSwitch LED bulbs, you can switch light settings without switching bulbs. Flip your existing switch to change from soft white light, to daylight, to a cozy warm glow. No dimmer or additional installation is required.

SceneSwitch

- SceneSwitch

Saves up to 80% energy

- Saves up to 80% energy

Long life

- Long Life

Application areas

- Application

No dimmer or additional installation needed

- No dimmer or additional installation needed

PHILIPS

Reflector
8-7-3W (65W) Medium Screw base, SceneSwitch, Non-dimmable

046677473662

Highlights

SceneSwitch

All-in-one replacement bulb that gives you three different light settings.

Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

Long Life



Reduce the hassle of replacing bulbs so often

Application

Ideal for any room in your home.

No dimmer/installation needed

Delivers a variety of light scenes straight out of the box to suit your different needs and moods. The technology is in the bulb itself, so no dimmer or other additional installation is required. Simply replace your bulb with this SceneSwitch bulb, and change between different scenes at a flick of your existing wall switch.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Bulb characteristics

- Dimmable: Non-dimmable
- Shape: Reflector
- Voltage: 120 V
- Wattage: 8W
- Wattage equivalent: 65W
- Base: Medium Screw base
- Indoor/Outdoor: Indoor
- Lamp shape code: BR30

Power consumption

- Power consumption per 1000h: 8 kW h
- Energy Star Certified
- Light output [lumen value]: 800 lm

Power

- Mercury content: 0 mg

Bulb dimensions

- Height: 5.2 inch
- Width: 3.74 inch

Durability

- Average life (at 2.7 hrs/day): 22.8 year(s)
- Lifetime of lamp: 25000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: General light
- Color: SceneSwitch
- Color rendering index (CRI): 80
- Color temperature: 2200-2700 K
- Starting time: 0 s
- Warm-up time to 60% light: 0

Rated values

- Rated lifetime: 25000 hour(s)



Issue date 2018-10-02

Version: 1.0.1

12 NC: 9290 013 75103
UPC: 0 46677 47366 2

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* Designed for the comfort of your eyes. Visit www.philips.com/eyecomfort for flicker, strobe and other criteria and product details.