



Philips LED
Reflector (Dimmable)

12W (90W)

E26
Bright White
Dimmable

046677530020



Bright LED lighting with excellent light quality

Create your desired ambiance with dimmable LED

Philips LEDspots are a perfect replacement for your halogen spot: they deliver halogen-like light and performance that you expect from the LED technology.

Instant on

- Instant on

Choose for high quality light

- Bright white light

Create the right light for your home

- Similar shape and size as halogen reflector

Comfortable LED light that is easy on your eyes

- Designed for the comfort of your eyes

PHILIPS

Reflector (Dimmable)
12W (90W) E26, Bright White, Dimmable

046677530020

Highlights

Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambiance to host friends or wind down with a book.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Cap/fitting: E26
- Dimmable
- Indoor/Outdoor: Indoor
- Voltage: 120 V
- Voltage: 120 V
- Wattage: 12
- Wattage equivalent: 90
- Lamp shape: Directional reflector
- Technology: LED

Bulb dimensions

- Height: 134 mm
- Width: 122 mm
- Number of switch cycles: 25000
- Weight: 0,394 kg

Durability

- Lifetime of lamps: 25000 hour(s)
- Number of switch cycles: 25000
- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7

Light characteristics

- Beam angle: 40 degree
- Color: Bright White
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Warm-up time to 60% light: Instant full light
- Starting time: 0.5 s
- Color consistency: 6 SDCM

Other characteristics

- Mercury content: 0 mg
- Lamp current: 112 mA
- Power factor: 0.8
- Efficacy: 75 K

Rated values

- Rated lifetime: 25000 hour(s)
- Rated beam angle: 40 degree
- Rated luminous flux: 900 lumen
- Rated power: 12 W



Issue date 2018-11-21

Version: 2.0.1

12 NC: 8670 001 55937

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* Designed for the comfort of your eyes. Visit www.philips.com/eyecomfort for flicker, strobe and other criteria and product details.