

Philips LED
Spot (Dimmable)

5.5W(35W)
GU5.3
Bright White
Dimmable

046677534516



Light that's easy on your eyes

Poor quality light could cause eye strain. It's more important than ever to properly light your home. Philips LED lamps fulfill stringent test criteria to ensure they meet our EyeComfort requirements* "

Choose for high quality light

- Bright white light

Choose a simple replacement for your old bulbs

- No UV or InfraRed

Light beyond illumination

- A simple LED for everyday use

Comfortable LED light that is easy on your eyes

- Designed for the comfort of your eyes

PHILIPS

Spot (Dimmable)
5.5W(35W) GU5.3, Bright White, Dimmable

046677534516

Highlights

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambiance to host friends or wind down with a book.

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

No UV or IR



The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

Specifications

Bulb characteristics

- Base: GU5.3
- Indoor/Outdoor: Indoor
- Wattage: 5.5
- Wattage equivalent: 35
- Technology: LED

Bulb dimensions

- Height: 44.5 mm
- Width: 50.5 mm
- Weight: 0,05 kg

Durability

- Number of switch cycles: 50000
- Lifetime of lamp: 15000 hour(s)
- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7

Light characteristics

- Beam angle: 35 degree
- Color: Bright White
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Warm-up time to 60% light: Instant full light
- Starting time: <0.5 s
- Color consistency: 6 SDCM

Other characteristics

- Mercury content: 0 mg
- Lamp current: 500 mA
- Power factor: 0.7
- Efficacy: 76 K

Rated values

- Rated lifetime: 15000 hour(s)
- Rated beam angle: 35 degree
- Rated luminous flux: 420 lumen
- Rated power: 5.5 W



Issue date 2018-11-30

Version: 1.0.1

12 NC: 8670 001 58759

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* Designed for the comfort of your eyes. Visit www.philips.com/eyecomfort for flicker, strobe and other criteria and product details.
* PstLM is smaller or equal to 1.0 measured according to IEC 61547-1 and IEC 61000-4-15.