

17" (16.0" VIS) XSD™ monitor

- 17-inch (16.0" VIS) color monitor with excellent front of screen performance for use with MACs and PCs
- Autoscan covers horizontal frequencies up to 70 kHz offering a maximum resolution of 1280 x 1024 with flicker free display of 1024 x 768 at up to 88 Hz
- Flat square High Contrast CRT with high-resolution 0.27 mm dot pitch (0.23 hdp)
- XSD-Xtra Space Design for large screen display in a small footprint: World's shortest 17-inch conventional monitor with maximum depth of only 408 mm/16.1"
- Multimedia Base and USB Hub option
- TCO99 certified



Optional Multimedia base 6G3B11

Optional USB HUB PCUH411

Let's make things better.



PHILIPS

17" (16.0" VIS) XSD™ monitor



Technical Specifications

CRT

- Size (inch/cm) 17"/ 41 cm
- Deflection angle (degrees) 90°
- Dot pitch 0.27 mm
- Horizontal pitch 0.23 mm
- Tube type Shadow mask, Flat Square, High Contrast, Anti Glare, Anti Static, Anti reflection, Light Transmission 47%
- Phosphor P22
- Recom. display area(mm) 306 x 230 mm
- Recom. display area(inch) 12.0" x 9.0"
- Max. display area(mm) 327 x 245 mm
- Max. display area(inch) 12.9" x 9.7"

Scanning

- Horizontal scanning 30 - 70 kHz
- Vertical scanning 50 - 160 Hz

Video

- Video dot rate 108 MHz
- Input impedance
 - Video 75 Ohm
 - Sync 2.2k Ohm
- Input signal levels 0.7 Vpp
- Sync input signal Separate sync
Composite sync
- Sync polarities Positive and negative

White color temperature

Chromaticity CIE coordinates:

- at 9300 K: x=0.283, y=0.297
- at 6500 K: x=0.313, y=0.329

Resolution and preset modes

- Max. resolution 1280 x 1024
- Recom. resolution 1024 x 768
- 16 user definable modes
- 22 factory preset modes:

	H.freq (kHz)/V.freq (Hz)
640 x 350	31.5K/70
640 x 350	37.9K/85
640 x 480	31.5K/60
640 x 480	37.9K/72
640 x 480	37.5K/75
640 x 480	43.3K/85
640 x 480	50.6K/100
720 x 400	31.5K/70
720 x 400	37.9K/85
800 x 600	37.9K/60
800 x 600	48.1K/72
800 x 600	46.9K/75
800 x 600	53.7K/85
800 x 600	63.9K/100
832 x 624	49.7K/75
1024 x 768	48.4K/60
1024 x 768	56.5K/70
1024 x 768	60.0K/75
1024 x 768	68.7K/85
1152 x 864	67.5K/75
1280 x 960	60.0K/60
1280 x 1024	64.0K/60

Plug and play compatibility

- Display Data Channel DDC 2B (VESA)
- Microsoft® Windows® 95/98/Me & 2000/NT/XP compatible
- sRGB

Power management

- Complies with EPA Energy Star and NUTEK specifications
- Operation 64 W (typical)
- Suspend/Stand By mode < 2 W
- Off mode/Deep Sleep < 2 W

Low-emission characteristics

- Complies with MPR-II and TCO '99 specifications

Monitor controls and functions

- Main 5-button OSD
Brightness +/- direct access
Contrast +/- direct access
- On Screen Display Language (English, Spanish, French, German, Italian, Chinese, Portuguese, Korean), zoom, horizontal, vertical, pincushion, balanced, trapezoid, parallelogram, color, reset, degauss, moire, serial number, resolution, frequency, sRGB

Connections and Cables

- Connections
 - Video 15-pin D-sub
- Cables D-Sub Video cable(fixed), power cord

Regulatory approvals

- TCO '99
- MPR-II Low Emission
- TÜV/GS, TÜV/Ergo, TÜV/9241-3
- FCC-B, UL, CSA, DHHHS
- SEMKO, Poland-B sign, C-Tick
- CE, BCIQ, PSB
- NUTEK, Energy Star

Physical specifications

- Dim. incl. base (WxHxD)(mm) 399 x 410 x 408
- Dim. incl. base (WxHxD)(inch) 15.7" x 16.1" x 16.1"
- Dim. excl. base (WxHxD)(mm) 399 x 373 x 408
- Dim. excl. base (WxHxD)(inch) 15.7" x 14.7" x 16.1"
- Weight (kg) 15.0 kg
- Power supply 90 - 264 VAC, 50/60Hz
- Temperature (operational) 0°C to 40°C/ 32°F to 104° F
- Temperature (storage) -25°C to 65°C/ -13°F to 149°F
- Relative humidity 5% to 95%
- MTBF > 75,000 H

Other

- USB Hub option type: PCUH411
- Multimedia Base option type: 6G3B11

As an Energy Star partner, Philips has determined that this product meets the Energy Star guidelines for energy efficiency.
Microsoft and Windows are registered trademarks of Microsoft Corporation.
All trademark acknowledged. Copyright 2001 Koninklijke Philips Electronics N.V.

All data subject to change without notice

Release date: May 2002

www.philips.com

Let's make things better.



PHILIPS