



Philips
PhotoFrame

25.9 cm/10.2" LCD

23.9 cm (9.4") v.area

10FF2CMI

Every picture tells your story

Larger screen for more viewing comfort! Display your digital photos in high pixel density quality, perfect digital color and all the richness of professional prints on the PhotoFrame 10FF2CMI's large screen.

Top quality display for print-like pictures

- High pixel density for sharp and detailed photo display
- Perfect digital colors for rich and stunning photo display

Luxurious design to complement your photos

- Exquisite materials and finishing add value to your photos
- Auto photo orientation to fit portrait or landscape modes

Easily display and manage your digital photos

- Play slideshows, single photo, thumbnails or show clock
- Create albums, slideshows and manage your photos
- Store up to 1000 photos in internal memory
- Rotate, zoom, crop, mask and add effects to your photos

Simple intuitive operation and great convenience

- Have fun with collages: display multiple photos in one view
- Copy photos among memory cards for extra storage
- Operate on AC power or cordlessly with rechargeable battery

PHILIPS
sense and simplicity

Highlights

High Pixel Density Display

The very best high density screen shows off your treasured photos with the same 'real life' rich detail and vibrant colors as high quality prints.

Perfect digital color

Full color display brings out the best in your photos with vibrant, real life colors by displaying the same full range of colors found in professionally printed photos.

Auto orientation

Automatic landscape/portrait recognition employs a sensor that recognizes PhotoFrame orientation and displays each photo in its proper mode.

Smart Album

Smart Album allows you to create and manage albums, as well as to set up and adjust transition effects to your photo slideshows.

Smart photo storage

Smart photo storage employs smart software that minimizes required storage space without compromising photo display quality.

PhotoEffect Wizard

The PhotoEffect Wizard is an easy-to-use feature that allows you to rotate, zoom in, crop and even adjust photo color tones to black & white or sepia right within PhotoFrame.



Specifications

Picture/Display

- Effective viewing area: 199.8 x 132.48 mm
- Resolution: viewing area resolution: 720 x 480
- Viewing angle: @ C/R > 10, 120° (H) / 110° (V)
- Lifetime, to 50% brightness: 20000 hr
- Brightness: 200 cd/m²
- Aspect ratio: 3:2
- Panel resolution: 800x480
- Pixel density: 91.5 ppi
- Contrast ratio (typical): 300:1

Connectivity

- USB: To PC/Mac (USB 2.0)

Storage Media

- Memory Card Types: Compact Flash type I, Secure Digital (SD), Secure Digital (SDHC), Multimedia Card, xD card, Memory Stick, Memory Stick Pro, Micro Secure Digital (SD), Memory Stick Duo (via adaptor), MS Pro Duo (via adaptor)
- Built-in memory capacity: 128MB (for 510-1020 photos, around 26MB used by system)

Convenience

- Card Reader: Built-in (2x)
- Photo format supported: JPEG photo, Up to 10MB JPEG files, Up to 16 Megapixels
- Placement: Landscape, Photo auto orientation, Portrait
- Buttons and controls: 2 buttons, 5-way mini joystick
- Playback mode: Full screen browse, Slideshow, Thumbnail browse
- Album management: Create, Delete, Edit, Rename
- Photo edit: Copy, Crop, Delete, Move, Rotate, Zoom & crop
- Photo effects: Black and White, Frames, Sepia
- Slideshow management: Create slideshow, Delete slideshow, Rename slideshow
- Slideshow setting: Collage (multiple pictures), Random, Sequential, Transition effect
- Screen background: Black, Gray, White
- Setup function: Auto on/off on weekday/weekend, Beep on/off, Brightness adjustment, Clock display enable/disable, Event reminder with snooze, Language, Photo source, Set time and date, Status
- System status: Battery level, Firmware version, Power source, Remaining memory
- Connected media status: Connected media,

Remaining memory

- Plug & Play Compatibility: Mac OS X, Windows 2000/XP or later, Windows Vista
- Regulatory approvals: BSMI, CCC, CE, C-Tick, FCC, GOST, PSB, UL, VCCI
- Adjustable stand: Rotating, Tilt-adjustable
- Other convenience: Kensington lock compatible
- Firmware upgradeable: Firmware upgradeable via USB
- On-Screen Display languages: Danish, Dutch, English, French, German, Italian, Japanese, Russian, Simplified Chinese, Spanish

Accessories

- Included accessories: AC-DC Adapter, PC/Mac software CD, Quick start guide, USB cable, User Manual

Dimensions

- Set dimensions with stand (W x H x D): 299 x 221 x 126 mm
- Set dimensions with stand in inch (W x H x D): 11.77 x 8.7 x 4.96 inch
- Weight: 1.37 kg
- Set weight (lb): 3.02 lb
- Temperature range (operation): 0°C to 45°C
- Temperature range (storage): -20°C to 60°C

Power

- Power consumption: (System on and battery charging) 7.5 W
- Operating time on battery: 1* hr
- Battery LED indicator: Charging - Blinking
- Power LED indicator: Operation - Blue
- Power mode supported: AC powered, Battery powered

Packaging dimensions

- Packaging dimensions (W x H x D): 13.4 x 7.1 x 10.7 inch
- Gross weight: 6.085 lb
- Nett weight: 3.968 lb
- Tare weight: 2.117 lb

Outer Carton

- Gross weight: 12.28 lb
- Outer carton (L x W x H): 15 x 14 x 11 inch
- Nett weight: 7.937 lb
- Tare weight: 4.343 lb



Issue date 2013-01-28

Version: 3.0.10

12 NC: 8670 000 33485
UPC: 6 09585 14181 0

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com