

PHILIPS

car headlight bulb

Ultinon LED

LED-HL [~HB3/HB4]

6000K

+160% brighter light

Compact design for better fit

11005ULX2

 Product Picture



The next level of white light

Compact and bright white LED

Philips Ultinon LED-HL [~HB3 HB4] headlights let you experience the next level of brightness: stylish white light with 6000 Kelvin and good headlight beam performance. Enhanced fit through compact design thanks to integrated electronics.

Bright LED headlights for cars

- Get 160% brighter light for superior visibility

Crisp white beam

- 6000 Kelvin color temperature for crisp white light

Long lasting LED headlights

- Durable LED bulbs for cars that last longer

Enhanced fit with compact design

- Easy installation thanks to integrated electronics

Reliable Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models
- For reflector headlights only.

Highlights

Brightness for improved vision

Driving in the dark is demanding, so you rely on your headlights. Forward and peripheral vision are both important to enhance your driving ability for a safer drive. With a bright beam, Philips Ultinon LED headlights for cars improve your visibility by up to 160%. Once you experience this daylight-like effect, you'll always prefer LED. The more you can see, the better you perform, the faster you react and the safer you are. So don't let darkness win, choose Philips and start driving at night with greater confidence and control.

Pure bright white light

With a high color temperature of up to 6000 Kelvin, the Philips Ultinon LED headlight produces a bright white, daylight-like beam. With clearer vision you're better able to spot obstacles and take the perfect driving line. And as you don't have to strain to see the terrain ahead, brighter lights make for a more comfortable and exciting night-time drive.

Durable LED headlight bulbs

You want bright and stylish headlights. But you don't want to keep replacing failed lamps. That's a major weakness of conventional headlights; the more powerful the light, the shorter its lifespan. LEDs last much longer, and Philips Ultinon LED products show superior durability: they last up to 8 years.

Compact design

Philips Ultinon LED uses a brand new bulb design integrating driver box electronics in the body. A driver box is the brain of an LED: it manages performance aspects such as wattage and light output. Many other LED Upgrades solutions in the market have the driver box exterior to the LED body. Philips Ultinon LED integrates it directly in the body to create an optimized design using minimal space. Optimized LED size is key because several optics are very small. Philips Ultinon

LED with its compact design fits a wide range of car models and can be easily installed by specialist mechanics.

Automotive grade quality



The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style. Enjoy a safer and smoother drive.

Ready - steady - installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible headlights with ease. However, it's recommended that you get your new Philips LED headlights installed by specialist mechanics – they will make sure you're ready to go. While these headlights are compatible with a wide range of existing car models, not all car types are supported.

For reflector headlights

The Philips Ultinon LED-HL [~HB3 HB4] lights are designed for reflector headlights. They are not recommended for projector headlight systems.

Specifications

Packaging Data

Packaging type: X2
EAN1: 8719018060280
EAN3: 8719018060297

Product description

Technology: LED
Application: High beam, Low beam
Range: Ultinon LED
Type: HB3/HB4
Homologation ECE: NO
Base: P20D; P22D
Technical features: Inbuilt Electronic driver
Designation LED Type: 11005ULX2

Electrical characteristics

Wattage: 15 W
Voltage: 12 V

Marketing specifications

Expected benefits: Compact design for better fit
Product highlight: The next level of white light

Light characteristics

Color temperature: Up to 6000K
Lumens: 1450

Ordering information

Order entry: 11005ULX2
Ordering code: 6028031

Lifetime

Life time: Up to 8 years

