

# PHILIPS

Car signaling bulb

Ultinon Pro6000 SI

LED-WHITE [~W21W]

Number of bulbs: 2

12V, 6000 K Cool White

Advanced automotive system



11065CU60X2



## Enjoy lasting brightness

Brighter, elegant signals

For a stylish drive, upgrade to Philips Ultinon Pro6000 LED-WHITE [~W21W] reverse, rear fog and stop lights. Their cool white color looks great and increases visibility so you can signal safely and stylishly.

### Superior visibility

- Signal your intent with brighter exterior lighting
- Instant safety information for other drivers
- Ergonomic design with three-LED array

### High-end, stylish signaling

- Upgrade your lights, upgrade your style

### Performance made to last

- Enhanced lifetime of up to 5,000 hours

### Simple plug-and-play replacement

- Easy to install and compatible with most car models
- Electrical compatibility with most cars

# Highlights

## Powerful brightness

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. And when poor weather reduces visibility, the need for bright and vibrant signaling becomes even greater. Philips Ultinon Pro6000 LED signaling lights provide you with bright lighting for signals. Your car says a lot about you, so make a style statement with Philips LED signaling lights.

## Instant-on technology

Compared to incandescent lamps, Philips Ultinon Pro6000 LEDs light up instantly to ensure that other drivers can react faster, keeping you safer.

## Uniform light distribution

For your reverse, rear fog and stop signals, Philips Ultinon Pro6000 LED gives you uniform light distribution. Its wide angle ensures that the light is projected where you need it.

## Elegant LED light

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're wanting to upgrade your style without buying a newer car, replacing your

exterior lighting with Philips Ultinon Pro6000 LED signals is a smart way to spend your money.

## Lifetime of up to 5,000 hours

You want bright, stylish car lights but you don't want to keep replacing failed lamps. That's a major weakness of conventional bulbs - the more powerful the light, the shorter its lifespan. Even at a higher light intensity, LEDs last much longer. Philips Ultinon Pro6000 LED lights are built to last. Due to features such as high-end LED technology and advanced heat-management systems, they last for up to 5,000 hours of operation.

## Ready, steady, installed!

Enjoy the plug-and-play experience: with Philips Ultinon Pro6000, bulb replacement is quick and easy.

## Electrical compatibility

LED retrofit and conventional bulbs differ from one another in terms of wattage, composition and power consumption. Replacing your conventional bulbs with other LEDs may prove problematic. Philips Ultinon Pro6000 bulbs are electrically compatible with most cars. Additional adapters are available as accessories for troubleshooting, if needed. We sell a complete solution.

# Specifications

## Lifetime

Life time: 5000 hrs

## Light characteristics

Color temperature: 6000 K

Lumens: 250

## Marketing specifications

Expected benefits: Brighter, elegant signals

Product highlight: Automotive Grade LED, Powerful brightness, Uniform light distribution

## Ordering information

Order entry: 11065CU60X2

Ordering code: 72126230

## Packaging Data

EAN1: 6974260721262

EAN3: 6974260721279

Packaging type: X2

## Outerpack information

Gross weight per piece: 0.51 kg

Net weight per piece: 360 g

Height: 13.5 cm

Length: 9.5 cm

Width: 1.5 cm

## Packed product information

Gross weight per piece: 36 g

Net weight per piece: 3 g

Height: 10.3 cm

Length: 14.2 cm

Width: 12.1 cm

MOQ (for professionals): 10 packs

Pack Quantity: 2 pcs

## Product description

Application: Reverse, Rear fog, Stop

Base: W3x16d

Designation: W21W LED white 11065 CU60 12V X2

Homologation ECE: NO

Range: Ultinon Pro6000 SI

Technology: LED

Voltage: 12 V

Type: LED-WHITE [-W21W]

