

# PHILIPS

Car signaling bulb

Ultinon Pro3000 SI

LED-White [~W21W]

Number of bulbs: 2

12V, 6000 K daylight effect

Advanced automotive system

11065U30CWB2



## Stand out from the crowd

### Durable and vibrant LED signaling

For a stylish drive, upgrade to Philips Ultinon Pro3000 LED [~W21W] reverse signals. They are bright and look good so you can signal safely and stylishly.

#### Bright LED lights

- Signal your intent with brighter exterior lighting

#### Good light distribution

- Optimized for enhanced visibility

#### Long lasting performance

- Durable, long-lasting LED lighting

#### Simple plug-and-play replacement

- Easy to install and compatible with many car models

# Highlights

## Bright and vibrant signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. And when poor weather reduces visibility, the need for bright and vibrant signaling becomes even greater. Philips Ultinon Pro3000 signaling lights provide you with a powerful daylight effect of up to 6000K, better illuminating the area immediately behind your car. And the more you can see, the safer you'll be.

## Good light distribution

The Philips Ultinon Pro3000 LED exterior lighting range is designed for smarter light distribution to project exterior signaling light where you need it (whether that's reversing, stopping, or signaling). With wide-angle,

uniform light, not only can you see more of the road, but other drivers can also see more of you.

## Ready, steady, installed!

Enjoy the plug-and-play experience: Philips Ultinon Pro3000 comes with standard caps so replacement is easy and quick.

## Long-lasting LED lighting

You want bright and stylish car lights, but you don't want to keep replacing failed lamps. That's a major weakness of conventional headlights – the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. Philips Ultinon Pro3000 LED lights are extremely durable with their lifetime of 3,000 hours.

# Specifications

## Packaging Data

EAN1: 8719018006707

EAN3: 8719018006714

Packaging type: B2

## Product description

Technology: LED

Application: Signaling and interior

Range: Ultinon Pro3000

Type: LED-White [-W21W]

Homologation ECE: NO

Designation: LED-White [-W21W]

Base: W3x16d

## Electrical characteristics

Wattage: 1,75 W

Voltage: 12 V

## Marketing specifications

Expected benefits: Style

Product highlight: Philips LED lamps

## Light characteristics

Color temperature: 6000 K

Lumens: 190

## Ordering information

Order entry: 11065U30CWB2

Ordering code: 00670730

## Outerpack information

Height: 10.3 cm

Length: 14.2 cm

Width: 12.1 cm

Gross weight per piece: 0.49 kg

## Packed product information

Gross weight per piece: 39.87 g

Height: 13.5 cm

Length: 9.5 cm

Net weight per piece: 10 g

Width: 1.5 cm

MOQ (for professionals): 10

Pack Quantity: 2

## Lifetime

Life time: 3000 hrs

