

PHILIPS

Signaling bulb

Ultinon LED

LED-S25 [~PY21W]

Number of bulbs: 2

12 V, amber intense

Turn signal

11065ULAX2



Bright signals. Stylish driving.

Durable LED quality

For a stylish drive, benefit from signaling lights with intense colors. Philips Ultinon LED [~W21W] turn indicator lights are bright, intense amber, and look good so you can signal in safety and with style.

Upgrade your style

- Upgrade your lights, upgrade your style

Brighter LED exterior lights

- Intense amber turn signals to be seen better
- Brighter signals for improved safety

Good light diffusion

- Good light distribution for enhanced visibility

Long lasting LED lights

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

Highlights

Stylish signaling colors

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for turning signals and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signaling LED lights.

Intense amber turn signals

Philips LED turn signals feature vibrant amber color performance that make your intentions clear to surrounding traffic. Amber intense means more safety for you and others around you.

Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it (whether that's reversing, stopping, or signaling). With wide angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with

ease. However, it's recommended that you get your new Philips X-tremeUltinon LED lights installed by specialist mechanics – they will make sure you're ready to go. While these lamps are compatible with a wide range of existing car models, not all car types are supported.

Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style.

Be seen with bright signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Bright signaling light ensures you are seen for improved safety. Whether it's reversing, positioning or stopping, Philips Ultinon LED signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements.

Specifications

Packaging Data

EAN1: 8719018050175

EAN3: 8719018050182

Packaging type: X2

Product description

Technology: LED

Application: Turn signal

Range: Ultinon LED

Type: [-W21W]

Homologation ECE: NO

Base: WX3x 16d

Designation LED Type: LED-T20 [-W21W]

Technical features: Instant on

Electrical characteristics

Voltage: 12 V

Marketing specifications

Expected benefits: Style

Product highlight: Bright signals Stylish driving

Light characteristics

Color temperature: Amber

Lumens: 22

Ordering information

Order entry: 11065ULAX2

Ordering code: 5017530

Outerpack information

Height: 8.5 cm

Length: 19.5 cm

Width: 15.1 cm

Gross weight per piece: 0.6 kg

Packed product information

Height: 9.2 cm

Length: 6.8 cm

Width: 2.8 cm

MOQ (for professionals): 20

Pack Quantity: 2

Lifetime

Life time: Up to 8 years

