



Philips Ultinon LED  
Signaling bulb

LED-T20 [~W21W]

Number of bulbs: 2  
12 V, red intense  
Stop, rear fog

11065ULRX2

## Bright signals. Stylish driving.

Durable LED quality

For a stylish drive, benefit from signaling lights with intense colors. Philips Ultinon LED [~W21W] stop lights are bright, intense red, and look good so you can signal in safety and with style.

### Upgrade your style

- Upgrade your lights, upgrade your style

### Brighter LED exterior lights

- Instantly on lights make rapid braking safer
- Brighter signals for improved safety

### Good light diffusion

- Good light distribution for enhanced visibility

### Long lasting LED lights

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

# PHILIPS

Signaling bulb  
LED-T20 [-W21W] Number of bulbs: 2, 12 V, red intense, Stop, rear fog

# Specifications

## Packaging Data

- EAN1: 8719018050076
- EAN3: 8719018050083
- Packaging type: X2

## Product description

- Technology: LED
- Range: Ultinon LED
- Type: W21W
- Homologation ECE: NO
- Base: WX3x 16d
- Application: Stop, rear fog
- Marking ECE: -
- Designation LED Type: LED-T20 [-W21W]
- Technical features: Instant on

## Electrical characteristics

- Wattage: 2.7 W
- Voltage: 12 V

## Marketing specifications

- Expected benefits: Advanced automotive system
- Product highlight: Bright signals Stylish driving

## Light characteristics

- Color temperature: Red
- Lumens: 80

## Ordering information

- Order entry: 11065ULRX2
- Ordering code: 5007630

## Outerpack information

- Height: 8.5 cm
- Length: 19.5 cm
- Width: 15.1 cm
- Gross weight per piece: 0.6 kg

## Packed product information

- Height: 9.2 cm
- Length: 6.8 cm
- Width: 2.8 cm
- MOQ (for professionals): 20
- Pack Quantity: 2

## Lifetime

- Life time: Up to 8 years

11065ULRX2

# Highlights

## Stylish signaling colors

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for turning signals and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signaling LED lights.

## Instantly on brake lights

Incandescent lamps take time to light up and reach peak performance. LED lights, on the other hand, are "instantly on". The difference is measured in fractions of a second. Under hard braking, fractions of a second matter. For example, at 100 km/h, just four tenths of a second difference in reaction time equates to an extra 11 meters of reaction distance – that's about 2.5 car lengths of extra thinking time. With Philips LED stop lights, as soon as you decide to brake, the driver behind will know.

## Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it (whether that's reversing, stopping, or signaling). With wide angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

## Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style.

## Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease. However, it's recommended that you get your new Philips XtremeUltinon LED lights installed by specialist mechanics – they will make sure you're ready to go. While these lamps are compatible with a wide range of existing car models, not all car types are supported.

## Be seen with bright signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Bright signaling light ensures you are seen for improved safety. Whether it's reversing, positioning or stopping, Philips Ultinon LED signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements.



Issue date 2019-07-26

Version: 8.1.1

12 NC: 8670 001 49578

© 2019 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.