

PHILIPS

Car signaling bulb

Ultinon Pro6000 SI

LED-WHITE [~W21/5W]

Number of bulbs: 2

12V, 6000 K Cool White

Advanced automotive system



11066CU60X2



Enjoy lasting brightness

Brighter, elegant signals

For a stylish drive, upgrade to Philips Ultinon Pro6000 LED-WHITE [~W21/5W] turn signals and position lights. Their cool white color looks great and increases visibility so you can signal safely and stylishly.

Superior visibility

- Signal your intent with brighter exterior lighting
- Instant safety information for other drivers
- Ergonomic design with three-LED array

High-end, stylish signaling

- Upgrade your lights, upgrade your style

Performance made to last

- Enhanced lifetime of up to 5,000 hours

Simple plug-and-play replacement

- Easy to install and compatible with most car models
- Electrical compatibility with most cars

Highlights

Powerful brightness

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. And when poor weather reduces visibility, the need for bright and vibrant signaling becomes even greater. Philips Ultinon Pro6000 LED signaling lights provide you with bright lighting for signals. Your car says a lot about you, so make a style statement with Philips LED signaling lights.

Instant-on technology

Compared to incandescent lamps, Philips Ultinon Pro6000 LEDs light up instantly to ensure that other drivers can react faster, keeping you safer.

Uniform light distribution

For your turn & position signals, Philips Ultinon Pro6000 LED gives you uniform light distribution. Its wide angle ensures that the light is projected where you need it.

Elegant LED light

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're wanting to upgrade your style without buying a newer car, replacing your exterior lighting with Philips Ultinon Pro6000 LED signals is a smart way to spend your money.

Lifetime of up to 5,000 hours

You want bright, stylish car lights but you don't want to keep replacing failed lamps. That's a major weakness of conventional bulbs - the more powerful the light, the shorter its lifespan. Even at a higher light intensity, LEDs last much longer. Philips Ultinon Pro6000 LED lights are built to last. Due to features such as high-end LED technology and advanced heat-management systems, they last for up to 5,000 hours of operation.

Ready, steady, installed!

Enjoy the plug-and-play experience: Philips Ultinon Pro6000 comes with standard caps and is polarity-free, so replacement is quick and easy.

Electrical compatibility

LED retrofit and conventional bulbs differ from one another in terms of wattage, composition and power consumption. Replacing your conventional bulbs with other LEDs may prove problematic. Philips Ultinon Pro6000 bulbs are electrically compatible with most cars. Additional adapters are available as accessories for troubleshooting, if needed. We sell a complete solution.

Specifications

Lifetime

Life time: 5000 hrs

Light characteristics

Color temperature: 6000 K

Lumens: 250/50

Marketing specifications

Expected benefits: Brighter, elegant signals

Product highlight: Automotive Grade LED, Powerful brightness, Uniform light distribution

Ordering information

Order entry: 11066CU60X2

Ordering code: 72140830

Packaging Data

EAN1: 6974260721408

EAN3: 6974260721415

Packaging type: X2

Outerpack information

Gross weight per piece: 0.51 kg

Net weight per piece: 360 g

Height: 13.5 cm

Length: 9.5 cm

Width: 1.5 cm

Packed product information

Gross weight per piece: 36 g

Net weight per piece: 3 g

Height: 10.3 cm

Length: 14.2 cm

Width: 12.1 cm

MOQ (for professionals): 10 packs

Pack Quantity: 2 pcs

Product description

Application: Front turn signal, Front position, Rear turn signal, Rear position/tail

Base: W3x16q

Designation: W21/5W LED white 11066 CU60 12V X2

Homologation ECE: NO

Range: Ultinon Pro6000 SI

Technology: LED

Voltage: 12 V

Type: LED-WHITE [-W21/5W]

