

PHILIPS

Car signaling bulb

Ultinon Pro3000 SI

LED-RED [~W21/5W]

Number of bulbs: 2

12V, Intense red light

Advanced automotive system

11066U30RB2



Stand out from the crowd

Durable and vibrant LED signaling

For a stylish drive, upgrade to Philips Ultinon Pro3000 LED [~W21/5W] stop and tail lights. They are bright, intense red, and look good so you can signal safely and stylishly.

Bright LED lights

- Signal your intent with brighter exterior lighting

Good light distribution

- Optimized for enhanced visibility

Long lasting performance

- Durable, long-lasting LED lighting

Simple plug-and-play replacement

- Easy to install and compatible with many car models

Highlights

Bright and vibrant signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Whether it's reversing, positioning or stopping, Philips Ultinon Pro3000 signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements. Upgrade your exterior lighting with a more intense red for stop and rear position lights. Your car says a lot about you, so make a style statement with Philips LED exterior signaling lights.

Good light distribution

The Philips Ultinon Pro3000 LED exterior lighting range is designed for smarter light distribution to project exterior signaling light where you need it (whether that's reversing, stopping, or signaling). With wide-angle,

uniform light, not only can you see more of the road, but other drivers can also see more of you.

Ready, steady, installed!

Enjoy the plug-and-play experience: Philips Ultinon Pro3000 comes with standard caps so replacement is easy and quick.

Long-lasting LED lighting

You want bright and stylish car lights, but you don't want to keep replacing failed lamps. That's a major weakness of conventional headlights - the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. Philips Ultinon Pro3000 LED lights are extremely durable with their lifetime of 3,000 hours.

Specifications

Packaging Data

EAN1: 8719018006387
EAN3: 8719018006394
Packaging type: B2

Product description

Technology: LED
Application: Signaling and interior
Range: Ultinon Pro3000
Type: LED-Red [-W21/5W]
Homologation ECE: NO
Designation: LED-Red [-W21/5W]
Base: W3x16q

Electrical characteristics

Wattage: 0.8/1.75 W
Voltage: 12 V

Marketing specifications

Expected benefits: Style
Product highlight: Philips LED lamps

Light characteristics

Color temperature: Red
Lumens: 50/20

Ordering information

Order entry: 11066U30RB2
Ordering code: 00638730

Outerpack information

Height: 10.3 cm
Length: 14.2 cm
Width: 12.1 cm
Gross weight per piece: 0.49 kg

Packed product information

Gross weight per piece: 39.87 g
Height: 13.5 cm
Length: 9.5 cm
Net weight per piece: 10 g
Width: 1.5 cm
MOQ (for professionals): 10
Pack Quantity: 2

Lifetime

Life time: 3000 hrs

