

# PHILIPS

Car signaling bulb

Ultinon Pro3000 SI

LED-RED [~W21/5W]

Number of bulbs: 2

12V, Intense red light

Advanced automotive system

11066U30RB2



## Stand out from the crowd

### Durable and vibrant LED signaling

For a stylish drive, upgrade to Philips Ultinon Pro3000 LED [~W21/5W] stop and tail lights. They are bright, intense red, and look good so you can signal safely and stylishly.

#### **Bright LED lights**

- Signal your intent with brighter exterior lighting

#### **Good light distribution**

- Optimized for enhanced visibility

#### **Long lasting performance**

- Durable, long-lasting LED lighting

#### **Simple plug-and-play replacement**

- Easy to install and compatible with many car models

# Highlights

## Bright and vibrant signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Whether it's reversing, positioning or stopping, Philips Ultinon Pro3000 signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements. Upgrade your exterior lighting with a more intense red for stop and rear position lights. Your car says a lot about you, so make a style statement with Philips LED exterior signaling lights.

## Good light distribution

The Philips Ultinon Pro3000 LED exterior lighting range is designed for smarter light distribution to project exterior signaling light where you need it (whether that's reversing, stopping, or signaling). With wide-angle,

uniform light, not only can you see more of the road, but other drivers can also see more of you.

## Ready, steady, installed!

Enjoy the plug-and-play experience: Philips Ultinon Pro3000 comes with standard caps so replacement is easy and quick.

## Long-lasting LED lighting

You want bright and stylish car lights, but you don't want to keep replacing failed lamps. That's a major weakness of conventional headlights - the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. Philips Ultinon Pro3000 LED lights are extremely durable with their lifetime of 3,000 hours.

# Specifications

## Packaging Data

**EAN1:** 8719018006387  
**EAN3:** 8719018006394  
**Packaging type:** B2

## Product description

**Technology:** LED  
**Application:** Signaling and interior  
**Range:** Ultinon Pro3000  
**Type:** LED-Red [-W21/5W]  
**Homologation ECE:** NO  
**Designation:** LED-Red [-W21/5W]  
**Base:** W3x16q

## Electrical characteristics

**Wattage:** 0.8/1.75 W  
**Voltage:** 12 V

## Marketing specifications

**Expected benefits:** Style  
**Product highlight:** Philips LED lamps

## Light characteristics

**Color temperature:** Red  
**Lumens:** 50/20

## Ordering information

**Order entry:** 11066U30RB2  
**Ordering code:** 00638730

## Outerpack information

**Height:** 10.3 cm  
**Length:** 14.2 cm  
**Width:** 12.1 cm  
**Gross weight per piece:** 0.49 kg

## Packed product information

**Gross weight per piece:** 39.87 g  
**Height:** 13.5 cm  
**Length:** 9.5 cm  
**Net weight per piece:** 10 g  
**Width:** 1.5 cm  
**MOQ (for professionals):** 10  
**Pack Quantity:** 2

## Lifetime

**Life time:** 3000 hrs

