

# PHILIPS

Signaling bulb

Ultinon LED

LED-T20 [~W21/5W]

Number of bulbs: 2

12 V, red intense

Stop/Tail

11066ULWX2



## Bright signals. Stylish driving.

### Durable LED quality

For a stylish drive, benefit from signaling lights with intense colors. Philips Ultinon LED [~W21/5W] stop & tail lights are bright, intense red, and look good so you can signal in safety and with style.

#### Upgrade your style

- Upgrade your lights, upgrade your style

#### Brighter LED exterior lights

- Instantly on lights make rapid braking safer
- Brighter signals for improved safety

#### Good light diffusion

- Good light distribution for enhanced visibility

#### Long lasting LED lights

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

# Highlights

## Stylish interior light

Your light requirements and taste may differ depending on the application. For the interior of your car, you can select from a variety of Philips Ultinon LED lamps for more brightness. Select a comfortable warm white 4000 Kelvin. Your car is an expression of who you are, so make a style statement with Philips interior LED lights.

## Be seen with bright signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Bright signaling light ensures you are seen for improved safety. Whether it's reversing, positioning or stopping, Philips Ultinon LED signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements.

## Instantly on brake lights

Incandescent lamps take time to light up and reach peak performance. LED lights, on the other hand, are "instantly on". The difference is measured in fractions of a second. Under hard braking, fractions of a second matter. For example, at 100 km/h, just four tenths of a second difference in reaction time equates to an extra 11 meters of reaction distance – that's about 2.5 car lengths of extra thinking time. With Philips LED stop lights, as soon as you decide to brake, the driver behind will know.

## Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it (whether that's reversing, stopping, or signaling). With wide angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

## Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease. However, it's recommended that you get your new Philips X-tremeUltinon LED lights installed by specialist mechanics – they will make sure you're ready to go. While these lamps are compatible with a wide range of existing car models, not all car types are supported.

## Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style.

# Specifications

## Packaging Data

**EAN1:** 8727900398878  
**EAN3:** 8727900398885  
**Packaging type:** X2

## Product description

**Technology:** LED  
**Application:** Stop/tail  
**Range:** Ultinon LED  
**Type:** W21/5W  
**Homologation ECE:** NO  
**Base:** WX3x 16d  
**Designation LED Type:** LED-T20 [-W21/5W]  
**Technical features:** Instant on

## Electrical characteristics

**Voltage:** 12 V

## Marketing specifications

**Expected benefits:** Advanced automotive system  
**Product highlight:** Bright signals Stylish driving

## Light characteristics

**Color temperature:** up to 6000K  
**Lumens:** 190

## Ordering information

**Order entry:** 11066ULWX2  
**Ordering code:** 39887830

## Outerpack information

**Height:** 8.5 cm  
**Length:** 19.5 cm  
**Width:** 15.1 cm  
**Gross weight per piece:** 0.6 kg

## Packed product information

**Height:** 9.2 cm  
**Length:** 6.8 cm  
**Width:** 2.8 cm  
**MOQ (for professionals):** 20  
**Pack Quantity:** 2

## Lifetime

**Life time:** Up to 8 years

