



Philips Connector rings  
LED-HL [~H7]  
Accessories for LED  
installation

**Type B**  
Compatible with most cars

**11172BX2**



## Easy to fit

Improves fit of LED headlights

H7 headlights feature a wide variety of lamp brackets, creating complexity at installation. With Philips connector rings, ensure that your bulbs fit the largest selection of car models.

### **Compatible with most car models**

- Connector rings for sure fit
- Check for compatibility with your car
- Check for compatibility with your car


### **Reliable Philips quality**

- Philips automotive lighting at the highest quality level
- Durable metal for long-lasting performance

# PHILIPS

## Highlights

### Model-specific connector rings



With H7 connector rings featuring a wide variety of lamp brackets, consumers face difficulties to fit some LED lights. Optional connector rings make sure that Philips LED bulbs fit the largest selection of car models to give you peace of mind and enjoy great light performance.

### Positive list online



On [www.philips.com/automotive](http://www.philips.com/automotive), you will find the relevant information to assess whether an optional connector ring is required for your car model. There are three versions available: Type A, supplied with the Philips LED-HL [H7]. Type B and Type C, separately sold options to ensure fit with additional car models. A positive list guides you to the correct choice. Type B is compatible with all Philips LED ranges.

### Long-lasting performance



Unlike most inferior quality connector rings, Philips Type B and C LED connector rings are made of durable metal, resistant to high temperatures. These connector rings have been tested in real-life automotive conditions so you can have confidence in their lasting performance and don't have to replace them as often.

### Automotive grade quality



The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style. Enjoy a safer and smoother drive.

### Easy to fit

There are four versions available: Type A, supplied with the Philips LED-HL [H7]. Type B, Type C and Type D separately sold options to ensure fit with additional car models. Type C is compatible with Philips Ultinon and Ultinon Essential LED-HL [~H7].

## Specifications

### Product description

- Technology: LED
- Application: High beam, Low beam
- Designation: 11172BX2
- Range: LED, Connector rings LED-HL [~H7]
- Type: Type B

### Marketing specifications

- Expected benefits: Sure fit
- Product highlight: LED connectors

### Ordering information

- Order entry: 11172BX2
- Ordering code: 5121930

### Packaging Data

- EAN1: 8719018051219
- EAN3: 8719018051226
- Packaging type: X2

### Packed product information

- Gross weight per piece: 80 g
- Height: 15.1 cm
- Length: 8.5 cm
- Net weight per piece: 60 g
- Width: 19.5 cm
- MOQ (for professionals): 10
- Pack Quantity: 2



Issue date 2019-10-09

Version: 6.3.1

12 NC: 8670 001 54266

© 2019 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.