

# PHILIPS

Car headlight bulb

Ultinon Pro5100

LED-HL [~H11]

5800K

Up to 160% brighter light

Compact design for perfect fit

11362U51X2



## Brightness to penetrate the dark White light for brighter roads

Generating brightness close to daylight levels, Philips Ultinon Pro5100 LED bulbs provide crystal-clear forward visibility without dazzling other road-users. Their brilliant white beam comes from a compact, easy-fit design.

### Clearer vision

- Up to 160% brighter light\*
- Experience improved visibility

### Brilliant white light

- 5800 Kelvin color temperature for crisp white light

### Long lasting performance

- Built to last up to 3,000 hours

### Enhanced fit with compact design

- Compact all-in-one design for plug-and-play use
- 12V- and 24V-compatible for wider usability

### Reliable Philips quality

- Philips automotive lighting for the highest quality

# Highlights

## 5800 K for crisp white light

With a high color temperature of up to 5800 Kelvin, the Philips Ultinon Pro5100 produces a bright white light that's close to daylight. The clearer vision this provides makes it easier to spot obstacles and take the perfect driving line. The optimal color temperature avoids tiring or straining the eyes, giving you more comfortable and safer night-time driving.

## Built to last

You want bright, stylish headlights but you don't want to keep replacing failed lamps. LED lights generate heat that must be managed. Philips AirFlux+ technology is a powerful cooling system with high thermal dispersion based on optimized materials and a high-performance coating. It diverts heat away from the light's critical components. Greater heat resistance enables Philips Ultinon LED to last longer than comparable products currently on the market. Philips Ultinon Pro5100 provides up to 3,000 hours' use.

## Compact all-in-one design

Philips Ultinon Pro5100 LED's brand-new design takes up minimal space in the headlamp unit. Its one-piece design, integrated electronics and robust heatsink make fitting easier, too. This bulb is compatible with a wide range of car models and can be easily installed by DIYers or specialist mechanics.

## Experience improved visibility

Beam pattern is just as important as brightness: a uniform, accurate beam pattern lets you see and be seen more clearly. Thanks to the perfect positioning of the LED chips on

Philips Ultinon Pro5100 bulbs, drivers have light exactly where they need it on the road without dazzling oncoming vehicles.

## 12V - 24V for wider usability

Philips Ultinon Pro5100 is compatible with 12V and 24V electrical systems, making it suitable for most vehicle types.

## Highest quality lighting

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. Philips Automotive Grade Quality products are designed and developed following strict quality-control processes, leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful, bright light and precise beam performance. You get high-end style. And you get an advanced LED lighting system for a safer, smoother, more enjoyable drive.

## Up to 160% brighter light\*

Take the strain out of driving at night. Philips Ultinon Pro5100 LED headlight bulbs offer razor-sharp vision without dazzling other road-users. More effective headlights enable you to spot hazards earlier, judge distances better and position your vehicle more accurately on the road. Featuring optimal color temperature and SafeBeam technology, these lamps generate a brilliant white beam close to daylight in its intensity. Experience visibility enhanced by up to 160%. So choose Philips for a safer, more satisfying drive in the dark.

# Specifications

## Marketing specifications

**Expected benefits:** Brighter Lights

**Product highlight:** Automotive Grade LED

## Product description

**Technology:** LED

**Type:** LED-HL [~H11]

**Application:** High beam, Low beam

**Designation:** LED H11 11362 U51 X2

**Range:** Ultinon Pro5100

**Base:** PGJ19-2

**Homologation ECE:** NO

## Electrical characteristics

**Wattage:** 12 W

**Voltage:** 13.2 V

## Light characteristics

**Lumens [lm]:** 1200

**Color temperature:** 5800K

## Lifetime

**Life time:** 3000 hrs

## Ordering information

**Order entry:** 11362U51X2

**Ordering code:** 72569731

## Packaging Data

**EAN1:** 6974260725697

**EAN3:** 6974260725703

**Packaging type:** X2

## Packed product information

**Gross weight per piece:** 190 g

**Length:** 11.1 cm

**Width:** 5 cm

**Height:** 16 cm

**Net weight per piece [g]:** 45

**MOQ (for professionals):** 6 packs

**Pack Quantity:** 2 pcs

## Outerpack information

**Height:** 15 cm

**Length:** 23.5 cm

**Width:** 16.8 cm

**Gross weight per piece:** 1.4 kg

