

# PHILIPS

car fog light bulb

Ultinon LED

LED-FOG [-H8/H11/H16]

6200 K

Up to 160% brighter light

Compact design for better fit



11366ULWX2



## The next level of white light

### Compact and bright white LED

Philips Ultinon LED fog lights let you experience the next level of brightness: stylish white light with up to 6200 Kelvin and good headlight beam performance. The compact design ensures an enhanced fit thanks to integrated electronics.

#### **Bright LED fog lights for cars**

- Get 160% brighter light for superior visibility

#### **Crisp white beam**

- 6200 Kelvin colour temperature for crisp white light

#### **Long-lasting LED fog lights**

- Durable LED bulbs for cars that last longer

#### **Enhanced fit with compact design**

- Easy installation thanks to integrated electronics

#### **Reliable Philips quality**

- Easy installation and compatible with many car models
- Philips automotive lighting at the highest quality level

# Highlights

## Brightness for improved vision

Driving in misty conditions is demanding, so you rely on your fog lights. Forward and peripheral vision are both important to enhance your driving ability for a safer drive. With SafeBeam technology, Philips Ultinon LED fog lights for cars improve your visibility by up to 160%. Once you experience this daylight-like effect, you'll always prefer LED. The more you can see, the better you perform, the faster you react and the safer you are. So don't let darkness win, choose Philips and start driving at night with greater confidence and control.

## Pure bright white light

With a high colour temperature of up to 6200 Kelvin, the Philips Ultinon LED fog lights produce a bright white, daylight-like beam. With clearer vision you're better able to spot obstacles and take the perfect driving line. And as you don't have to strain to see the terrain ahead, brighter lights make for a more comfortable and exciting night-time drive.

## Durable LED fog light bulbs

You want bright and stylish fog lights. But you don't want to keep replacing failed lamps. That's a major weakness of conventional fog lights; the more powerful the light, the shorter its lifespan. LEDs last much longer, and Philips Ultinon LED products with AirFlux heat management show superior durability: they last up to 8 years.

## Compact design

Philips Ultinon LED uses a brand-new bulb design, integrating driver box electronics in the body. A driver box is the brain of an LED: it

manages performance aspects such as wattage and light output. Many other LED Upgrades solutions on the market have the driver box exterior to the LED body. Philips Ultinon LED integrates it directly in the body to create an optimised design using minimal space. Optimised LED size is key because several optics are very small. Philips Ultinon LED, with its compact design, fits a wide range of car models and can easily be installed by specialist mechanics.

## Automotive-grade quality

The technologically advanced Philips lighting is renowned in the automotive industry and has been for over 100 years. The Philips Automotive-Grade Quality products are designed and developed following strict quality-control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful, bright light, and precise beam performance. You get high-end style. Enjoy a safer and smoother drive.

## Ready, steady, installed!

Designed to be easily installed in compatible vehicles, so drivers with maintenance experience will be able to upgrade compatible headlights with ease. However, it's recommended that you get your new Philips LED headlights installed by specialist mechanics – they will make sure you're ready to go. While these headlights are compatible with a wide range of existing car models, not all car types are supported.

# Specifications

## Packaging Data

**Packaging type:** X2  
**EAN1:** 8727900398632  
**EAN3:** 8727900398649

## Product description

**Technology:** LED  
**Application:** Front fog  
**Range:** Ultinon LED  
**Type:** FOG [-H8/H11/H16]  
**Homologation ECE:** NO  
**Base:** PGJ19-1; PGJ19-2; PGJ19-3  
**Designation LED Type:** LED-FOG [-H8/H11/H16]  
**Technical features:** Inbuilt Electronic driver

## Electrical characteristics

**Voltage:** 12 V

## Marketing specifications

**Expected benefits:** Style  
**Product highlight:** The next level of white light

## Light characteristics

**Colour temperature:** Up to 6200 K

## Ordering information

**Order entry:** 11366ULWX2  
**Ordering code:** 39863231

## Lifetime

**Life time:** Up to 8 years

