



Philips X-tremeUltinon
LED gen2
car signalling bulb

LED-AMB [~PY21W] +CANbus

Number of bulbs: 2
12 V, amber intense
Advanced automotive system

11498XUAXM



Brighter and more stylish

Strong, durable and vibrant LED signalling

For safe and modern driving, change to intense amber Philips X-tremeUltinon LED gen2 turn signals [~PY21W]. They are powerful and precise and look good, so you can signal in safety and with style. This version includes a warning canceller.

Brighter LED exterior lights

- Signal your intent with brighter exterior lighting
- Intense amber indicators to be seen better
- Instantly on lights make direction changes safer

Upgrade your style

- Upgrade your lights, upgrade your style

Superior light diffusion

- Uniform light distribution for enhanced visibility

Longer-lasting LED lights

- Durable and long-lasting LED lighting

Exceptional Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation with smart adapter for car compatibility

PHILIPS

Highlights

Bright and vibrant signals

Signalling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. And when poor weather conditions reduce visibility, the need for bright and vibrant signalling becomes even more important. Philips X-tremeUltinon LED gen2 signalling lights provide you with bright daylight effect and up to 6000 K for reverse and positioning lights. With more intense colours for turn and stop applications, instantly on LEDs and a uniform and well directed light, you'll give other drivers vital extra time to react to your movements.

Stylish signalling colours

While the main goal of exterior lighting is to help you see and be seen, there is no reason why you should not look good at the same time. If you are looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for indicators and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signalling LED lights.

Intense amber indicators

Philips LED indicators feature vibrant amber colour performance that make your intentions clear to surrounding traffic. Amber intense means more safety for you and others around you.

Instantly on turn signals

Incandescent lamps take time to light up and reach peak performance. LED lights, on the other hand, are "instantly on". The difference is measured in fractions of a second. When you need to react quickly, fractions of a second matter. For example, at 100 km/h (62 mph), just four tenths of a second difference in reaction time equates to an extra 11 metres (36 feet) of reaction distance — that's about 2.5 car lengths of extra thinking time. With Philips LED lights, as soon as you signal to change directions, the driver behind will know.

Uniform light distribution

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signalling light is projected where you need it (whether that is reversing, stopping, or signalling). With wide angle and uniform light diffusion, not only can you see more of the road, other drivers can see more of you.

Automotive-grade quality

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. Philips Automotive-Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips bulbs, because when you buy Philips, you buy quality. You get powerful bright light and precise beam performance. You get high-end style. And you get an advanced LED lighting system for a safer, smoother and more enjoyable drive.

Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease. Thanks to the unique Smart CANbus adapter specifically designed for turn signals, you make sure that your turn signals function well and provide safety information for your car.

Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional headlights; the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer, and Philips X-tremeUltinon LED gen2 lights are extremely durable. Due to the latest technological innovation, they prevent heat and vibrational damage and last for up to 12 years. With most cars replaced or upgraded within that time, your stylish new lights should last for your car's lifetime.

Specifications

Packaging Data

- EAN1: 8719018051592
- EAN3: 8719018051608
- Packaging type: XM

Product description

- Technology: LED
- Application: Indicator
- Range: X-tremeUltinon LED gen2
- Type: PY21W
- Homologation ECE: NO
- Base: BAU15s
- Designation LED Type: LED-AMB [~PY21W] +CANbus
- Technical features: instant on

Electrical characteristics

- Voltage: 12 V
- Wattage: 1.8 W

Marketing specifications

- Expected benefits: Advanced automotive system
- Product highlight: Brighter, vibrant signals

Light characteristics

- Colour temperature: Amber intense
- Lumens [lm]: 180

Ordering information

- Order entry: 11498XUAXM
- Ordering code: 05159230

Outer pack information

- Height: 8.5 cm
- Length: 21.1 cm
- Width: 19.1 cm
- Gross weight per piece: 2.55 kg

Packed product information

- Height: 9.2 cm
- Length: 6.8 cm
- Width: 4.3 cm
- MOQ (for professionals): 20
- Pack Quantity: 2
- Gross weight per piece [g]: 248
- Net weight per piece [g]: 114

Lifetime

- Life time: Up to 12 years



Issue date 2019-08-25

Version: 9.1.1

12 NC: 8670 001 56958

© 2019 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.