

PHILIPS

NORELCO

Wet & dry electric shaver, Series 6000

Shaver 6600


DualPrecision heads

GyroFlex 2D contouring system

50 min shaving, 1 hour charge

JetClean system

1160X/42



Series 6000 – Soft touch, smooth shave with Jet Clean system

The Philips Norelco Shaver 6600 (formerly called SensoTouch 2D) has a soft touch for a smooth shave. The Gyroflex 2D system adjusts easily to your face and the JetClean System washes, lubricates, dries and charges your shaver.

Designed for comfort

- Shaver follows the contours of your face

Innovative technology for a closer shave

- Shaves even the shortest stubble
- Gets below the skin, for a closer shave

Protective seal for wet or dry shaving

- Comfortably shaves – wet or dry

Cordless convenience

- One-hour charge provides up to 50 minutes of shaving

Easy cleaning with Jet Clean

- Jet Clean system cleans, lubricates, and charges the razor



asimpleswitch.com



asimpleswitch.com

Highlights

GyroFlex 2D system



Designed to follow the curves of your face, this wet and dry electric shaver uses GyroFlex 2D's two-dimensional contouring technology to pivot in a circular motion and tilt inwards. Its contour-following system adjusts easily to every curve, minimizing both pressure and irritation. The result is a close shave that's easy on your skin.

DualPrecision shaving heads



This shaver delivers a close, comfortable shave with complete coverage and accuracy. It features DualPrecision heads with slots to shave the normal hairs and holes to shave even the shortest stubble.

Super Lift & Cut action



The patented Super Lift and Cut dual blade system lifts hairs to cut comfortably below skin level, while the low-friction SkinGlide shaving surface slides smoothly along your skin. As a finishing touch, use the precision-trimmer feature for your mustache and sideburns.

Aquatec - Wet or Dry shaving



This shaver lets you shave any way you want. The AquaTec seal gives you the option of either a comfortable dry shave or a refreshing wet shave with shaving cream or gel. No matter which you choose, Series 6000's slim, non-slip grip makes for easy handling.

Rechargeable cordless



With SensoTouch, you'll enjoy the convenience of cordless operation. One hour of charging provides up to 50 minutes of shaving

time, and a 3-minute quick-charge option gives you enough power for a single shave. The two-level battery display lets you know when the battery is full and shows a low-battery warning when it's time to recharge.

Jet Clean system



SensoTouch is easy to maintain with a Jet Clean system that cleans, lubricates, and charges the shaver. Additionally, SensoTouch features a hair collection chamber that helps keep your sink tidy.

Great for travel

An excellent travel companion, the SensoTouch features a travel lock, protective cap, and storage pouch for safe portability. SensoTouch also has a worldwide voltage function that automatically adjusts from 100 volts to 240 volts AC, making it ideal for international trips.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Shaving Performance

Contour following: GyroFlex 2D contour following

Shaving system: DualPrecision System, Patented Super Lift & Cut

Styling: Precision trimmer

SkinComfort: SkinGlide

Ease of use

Charging: 1 hour, Rechargeable, Cordless, Quick charge

Shaving time: Up to 17 days

Display: 2 level battery indicator, Battery low indicator, Charge indicator, Travel lock

Wet & Dry: Wet and dry use, Jet Clean

Cleaning: Washable

Jet Clean: Cleans, lubricates and charge

Design

Handle: Slim handle, Anti-slip grip

Finishing: Seamless foil, LED Display

Color: Grey

Accessories

Stand: Charging stand

Pouch: Soft pouch

Maintenance: Cleaning brush, Protective cap

Jet Clean

Power

Battery Type: Lithium-ion

Run time: 50 min

Stand-by power: 0.15 W

Max power consumption: 5,4 W

Service

2-year guarantee

Replacement head: Replace every yr with RQ11

