

# PHILIPS

Car signaling bulb

Ultinon Pro3000 SI



LED-FEST 38mm [-C5W]

Number of bulbs: 1

12V, 6000 K daylight effect

Advanced automotive system

11854U30CWB1



## Stand out from the crowd

### Durable and vibrant LED signaling

For a stylish drive, upgrade to Philips Ultinon Pro3000 LED 38mm festoons for interior lighting. The strong 6000 K bright white light illuminates the inside of your car, while being kind to your eyes.

#### **Bright LED lights**

- Bright lights for the interior of your car

#### **Good light distribution**

- Optimized for enhanced visibility

#### **Long lasting performance**

- Durable, long-lasting LED lighting

#### **Simple plug-and-play replacement**

- Easy to install and compatible with many car models

# Highlights

## Bright interior light

Select our bright white Philips Ultinon Pro3000 LED lamps for superior visibility and style inside your car. Bright and stylish, these lights will transform your driving experience. Whether you're searching for a dropped phone, your passengers want to read, or you're trying to work out the best route to your destination, you can now enjoy bright interior light.

## Good light distribution

Philips Ultinon Pro3000 LED interior lights provide a powerful daylight effect of up to 6000 K, illuminating your car's passenger compartment with bright, uniform, stylish light.

## Ready, steady, installed!

Enjoy the plug-and-play experience: Philips Ultinon Pro3000 comes with standard caps so replacement is easy and quick.

## Long-lasting LED lighting

You want bright and stylish car lights, but you don't want to keep replacing failed lamps. That's a major weakness of conventional headlights - the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. Philips Ultinon Pro3000 LED lights are extremely durable with their lifetime of 3,000 hours.

# Specifications

## Packaging Data

**EAN1:** 8719018006646  
**EAN3:** 8719018006653  
**Packaging type:** B1

## Product description

**Technology:** LED  
**Application:** Signaling and interior  
**Range:** Ultinon Pro3000  
**Type:** LED-FEST 38mm [-C5W]  
**Homologation ECE:** NO  
**Designation:** LED-FEST 38mm [-C5W]  
**Base:** SV8.5 Ø9.8 x 38 mm

## Electrical characteristics

**Wattage:** 0.6 W  
**Voltage:** 12 V

## Marketing specifications

**Expected benefits:** Style  
**Product highlight:** Philips LED Signaling lamps

## Light characteristics

**Color temperature:** 6000 K  
**Lumens:** 50

## Ordering information

**Order entry:** 11854U30CWB1  
**Ordering code:** 00664630

## Outerpack information

**Height:** 10.3 cm  
**Length:** 14.2 cm  
**Width:** 12.1 cm  
**Gross weight per piece:** 0.23 kg

## Packed product information

**Gross weight per piece:** 12.27 g  
**Height:** 13.5 cm  
**Length:** 9.5 cm  
**Net weight per piece:** 2.4 g  
**Width:** 1.5 cm  
**MOQ (for professionals):** 10  
**Pack Quantity:** 1

## Lifetime

**Life time:** 3000 hrs

