

PHILIPS

Car signaling bulb

Ultinon Pro3000 SI



LED-FEST 38mm [-C5W]

Number of bulbs: 1

12V, 6000 K daylight effect

Advanced automotive system

11854U30CWB1



Stand out from the crowd

Durable and vibrant LED signaling

For a stylish drive, upgrade to Philips Ultinon Pro3000 LED 38mm festoons for interior lighting. The strong 6000 K bright white light illuminates the inside of your car, while being kind to your eyes.

Bright LED lights

- Bright lights for the interior of your car

Good light distribution

- Optimized for enhanced visibility

Long lasting performance

- Durable, long-lasting LED lighting

Simple plug-and-play replacement

- Easy to install and compatible with many car models

Highlights

Bright interior light

Select our bright white Philips Ultinon Pro3000 LED lamps for superior visibility and style inside your car. Bright and stylish, these lights will transform your driving experience. Whether you're searching for a dropped phone, your passengers want to read, or you're trying to work out the best route to your destination, you can now enjoy bright interior light.

Good light distribution

Philips Ultinon Pro3000 LED interior lights provide a powerful daylight effect of up to 6000 K, illuminating your car's passenger compartment with bright, uniform, stylish light.

Ready, steady, installed!

Enjoy the plug-and-play experience: Philips Ultinon Pro3000 comes with standard caps so replacement is easy and quick.

Long-lasting LED lighting

You want bright and stylish car lights, but you don't want to keep replacing failed lamps. That's a major weakness of conventional headlights - the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. Philips Ultinon Pro3000 LED lights are extremely durable with their lifetime of 3,000 hours.

Specifications

Packaging Data

EAN1: 8719018006646
EAN3: 8719018006653
Packaging type: B1

Product description

Technology: LED
Application: Signaling and interior
Range: Ultinon Pro3000
Type: LED-FEST 38mm [-C5W]
Homologation ECE: NO
Designation: LED-FEST 38mm [-C5W]
Base: SV8.5 Ø9.8 x 38 mm

Electrical characteristics

Wattage: 0.6 W
Voltage: 12 V

Marketing specifications

Expected benefits: Style
Product highlight: Philips LED Signaling lamps

Light characteristics

Color temperature: 6000 K
Lumens: 50

Ordering information

Order entry: 11854U30CWB1
Ordering code: 00664630

Outerpack information

Height: 10.3 cm
Length: 14.2 cm
Width: 12.1 cm
Gross weight per piece: 0.23 kg

Packed product information

Gross weight per piece: 12.27 g
Height: 13.5 cm
Length: 9.5 cm
Net weight per piece: 2.4 g
Width: 1.5 cm
MOQ (for professionals): 10
Pack Quantity: 1

Lifetime

Life time: 3000 hrs

