

PHILIPS

Car signaling bulb

Ultinon Pro3000 SI



LED-T10 [-W5W]

Number of bulbs: 2

12V, 6000 K daylight effect

Advanced automotive system

11961U30CWB2



Stand out from the crowd

Durable and vibrant LED signaling

For a stylish drive, upgrade to Philips Ultinon Pro3000 LED [-W5W] position lights. They are daylight-bright and look good so you can signal safely and stylishly.



Bright LED lights

- Signal your intent with brighter exterior lighting

Good light distribution

- Optimized for enhanced visibility

Long lasting performance

- Durable, long-lasting LED lighting

Simple plug-and-play replacement

- Easy to install and compatible with many car models

Highlights

Bright and vibrant signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. And when poor weather reduces visibility, the need for bright and vibrant signaling becomes even greater. Philips Ultinon Pro3000 LED signaling lights provide you with a bright daylight effect plus up to 6000 K for positioning and interior lighting. Your car says a lot about you, so make a style statement with Philips LED signaling lights.

Good light distribution

Whether it's for parking lights, glove compartment, dashboard or trunk lighting, Philips Ultinon Pro3000 LED gives you

uniform light distribution. Its wide angle ensures that the light is projected where you need it.

Ready, steady, installed!

Enjoy the plug-and-play experience: Philips Ultinon Pro3000 comes with standard caps so replacement is easy and quick.

Long-lasting LED lighting

You want bright and stylish car lights, but you don't want to keep replacing failed lamps. That's a major weakness of conventional headlights - the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. Philips Ultinon Pro3000 LED lights are extremely durable with their lifetime of 3,000 hours.

Specifications

Packaging Data

EAN1: 8719018006929
EAN3: 8719018006936
Packaging type: B2

Product description

Technology: LED
Application: Signaling and interior
Range: Ultinon Pro3000
Type: LED-T10 [-W5W]
Homologation ECE: NO
Designation: LED-T10 [-W5W]
Base: W21x9.5d

Electrical characteristics

Wattage: 0.6 W
Voltage: 12 V

Marketing specifications

Expected benefits: Style
Product highlight: Philips LED Signaling lamps

Light characteristics

Color temperature: 6000 K
Lumens: 55

Ordering information

Order entry: 11961U30CWB2
Ordering code: 00692930

Outerpack information

Height: 10.3 cm
Length: 14.2 cm
Width: 12.1 cm
Gross weight per piece: 0.49 kg

Packed product information

Gross weight per piece: 14.47 g
Height: 13.5 cm
Length: 9.5 cm
Net weight per piece: 2.3 g
Width: 1.5 cm
MOQ (for professionals): 10
Pack Quantity: 2

Lifetime

Life time: 3000 hrs

