



Philips Ultinon LED  
Interior and signaling bulb

**LED-T10 [~W5W]**

Number of bulbs: 2  
12 V, 6000 K daylight effect  
Position, interior

**11961ULWX2**



## Bright signals. Stylish driving.

### Durable LED quality

For a stylish drive, benefit from signaling lights with intense colors. Philips Vision LED T10 interior & positioning lights with 6000 K daylight effect are bright and look good so you can signal in safety and with style.

#### **Upgrade your style**

- Upgrade your lights, upgrade your style

#### **Brighter LED exterior lights**

- Brighter signals for improved safety

#### **Good light diffusion**

- Good light distribution for enhanced visibility

#### **Durable Philips quality**

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

#### **Long lasting LED lights**

- Durable and long-lasting LED lighting

# PHILIPS

# Specifications

## Packaging Data

- EAN1: 8727900398816
- EAN3: 8727900398823
- Packaging type: X2

## Product description

- Technology: LED
- Range: Ultinon LED
- Type: W5W
- Homologation ECE: NO
- Base: W2,1x9,5d
- Application: Position, interior
- Designation LED Type: LED-T10 [~W5W]

## Electrical characteristics

- Voltage: 12 V

## Marketing specifications

- Expected benefits: Advanced automotive system
- Product highlight: Bright signals Stylish driving

## Light characteristics

- Color temperature: Up to 6000K
- Lumens: 50

## Ordering information

- Order entry: 11961ULWX2
- Ordering code: 39881630

## Outerpack information

- Height: 8.5 cm
- Length: 19.5 cm
- Width: 15.1 cm
- Gross weight per piece: 0.37 kg

## Packed product information

- Height: 9.2 cm
- Length: 6.8 cm
- Width: 2.8 cm
- MOQ (for professionals): 20
- Pack Quantity: 2

## Lifetime

- Life time: Up to 8 years

# Highlights

## Stylish signaling lights

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're looking to upgrade your style, without buying a newer car, replacing your interior and exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for turning signals and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signaling LED lights.

## Be seen with bright signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Bright signaling light ensures you are seen for improved safety. Whether it's reversing, positioning or stopping, Philips Vision LED signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements.

## Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional headlights; the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last longer. And Philips Vision LED lights have additional resistance to heat and vibration, making them a perfect choice for long-lasting performance.

## Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it (whether that's reversing, stopping, or signaling). With wide angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

## Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light. You get high-end style.

## Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease.



Issue date 2019-04-24

Version: 4.0.1

12 NC: 8670 001 49686

© 2019 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.