

# PHILIPS

## Car signaling bulb

### Ultinon Pro6000 SI

LED-T10 [~W5W]

Number of bulbs: 2

12V, 8000 K Cool Blue

Advanced automotive system



11961XU60X2



## Enjoy lasting brightness

Brighter, elegant signals

For a stylish drive, upgrade to Philips Ultinon Pro6000 LED [~W5W] position lights. They are bright and elegant so you can signal safely and stylishly.

#### **Superior visibility**

- Signal your intent with brighter exterior lighting
- Ergonomic design with three-LED array

#### **High-end, stylish signaling**

- Upgrade your lights, upgrade your style

#### **Performance made to last**

- Enhanced lifetime of up to 5,000 hours
- HeatShield ensures durable performance

#### **Simple plug-and-play replacement**

- Electrical compatibility with most cars
- Easy to install and compatible with most car models

# Highlights

## Powerful brightness

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. And when poor weather reduces visibility, the need for bright and vibrant signaling becomes even greater. Philips Ultinon Pro6000 LED signaling lights provide you with a bright cool blue effect plus up to 8000 K for positioning and interior lighting. Your car says a lot about you, so make a style statement with Philips LED signaling lights.

## Uniform light distribution

Whether it's for parking lights, glove compartment, or interior lighting, Philips Ultinon Pro6000 LED gives you uniform light distribution. Its wide angle ensures that the light is projected where you need it.

## Elegant LED light

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're wanting to upgrade your style without buying a newer car, replacing your exterior lighting with Philips Ultinon Pro6000 LED signals is a smart way to spend your money.

## Lifetime of up to 5,000 hours

You want bright, stylish car lights but you don't want to keep replacing failed lamps. That's a major weakness of conventional bulbs – the more powerful the light, the

shorter its lifespan. Even at a higher light intensity, LEDs last much longer. Philips Ultinon Pro6000 LED lights are built to last. Due to features such as high-end LED technology and advanced heat-management systems, they last for up to 5,000 hours of operation.

## Good at handling heat

With HeatShield technology, Philips Ultinon Pro6000 T10 bulbs are resistant to high temperatures even when installed next to headlight bulbs. Made with a special composite material, they can endure any thermal challenge and still offer high performance.

## Electrical compatibility

LED retrofit and conventional bulbs differ from one another in terms of wattage, composition and power consumption. Replacing your conventional bulbs with other LEDs may prove problematic. Philips Ultinon Pro6000 bulbs are electrically compatible with most cars. Additional adapters are available as accessories for troubleshooting, if needed. We sell a complete solution.

## Ready, steady, installed!

Enjoy the plug-and-play experience: Philips Ultinon Pro6000 comes with standard caps and is polarity-free, so replacement is quick and easy.

# Specifications

## Lifetime

**Life time:** 5000 hrs

## Light characteristics

**Color temperature:** 8000 K

**Lumens:** 60

## Marketing specifications

**Expected benefits:** Brighter, elegant signals  
**Product highlight:** Automotive Grade LED, Powerful brightness, HeatShield, Uniform light distribution

## Ordering information

**Order entry:** 11961XU60X2

**Ordering code:** 72164430

## Packaging Data

**EAN1:** 6974260721644

**EAN3:** 6974260721651

**Packaging type:** X2

## Outerpack information

**Gross weight per piece:** 0.37 kg

**Net weight per piece:** 240 g

**Height:** 13.5 cm

**Length:** 9.5 cm

**Width:** 1.5 cm

## Packed product information

**Gross weight per piece:** 24 g

**Net weight per piece:** 3 g

**Height:** 10.3 cm

**Length:** 14.2 cm

**Width:** 12.1 cm

**MOQ (for professionals):** 10 packs

**Pack Quantity:** 2 pcs

## Product description

**Application:** Interior lights, Front parking/position lights, Dashboard light, Glove compartment light, Trunk lights and license plate, 3rd stop light, Side indicators  
**Base:** W21x9.5d

**Designation:** W5W LED white 11961 XU60 12V X2

**Homologation ECE:** NO

**Range:** Ultinon Pro6000 SI

**Technology:** LED

**Voltage:** 12 V

**Type:** LED-T10 [-W5W]

