



Philips Vision Moto
Motorcycle headlights

Type of lamp: S3

Pack of: 1
12 V, 15 W

12008C1



Feel safe, ride safe

Up to 30% more vision

Producing up to 30% more vision than a standard lamp, Vision Moto headlamps allow motorcycle riders to see farther with improved light beam performance at a very competitive price. For greater safety, choose Vision Moto bulbs!

The most economical choice

- The best value choice
- Up to 30% more vision

State-of-the-art technology

- Philips is the choice of major motorbike manufacturers.
- Respecting the high quality standards of ECE homologation

Up to 30% more vision than a standard lamp

- Philips moto lamps are made of high-quality quartz glass

PHILIPS

Motorcycle headlights
Type of lamp: S3 Pack of: 1, 12 V, 15 W

Specifications

Packaging Data

- Packaging type: C1
- EAN1: 8711500773944
- EAN3: 8711500779335

Light characteristics

- Lumens: 240

Marketing specifications

- Expected benefits: More Vision
- Product highlight: Up to 30% more vision

Product description

- Designation: S3 Vision Moto
- Range: Vision Moto
- Technology: Halogen
- Base: P26s
- Application: High beam, Low beam
- Type: S3

Lifetime

- Lifespan: Up to 110 h

Electrical characteristics

- Voltage: 12 V
- Wattage: 15 W

Ordering information

- Ordering code: 77394430
- Order entry: 12008C1

Packed product information

- Gross weight per piece: 211.67 g
- Height: 7.6 cm
- Length: 4.55 cm
- Width: 4.55 cm

Outer pack information

- Height: 7.8 cm
- Length: 23.8 cm
- Width: 9.3 cm

12008C1

Highlights

Best value



The Philips Vision Moto lamps are the best choice for drivers looking for economical lamp solutions and not willing to compromise on security. The motorcycle bulbs offer 30% more vision on the road than a standard lamp.

ECE homologation

Philips Automotive is dedicated to producing best-in-class products and services in the Original Equipment Manufacturer market as well as in the aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximise the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements.

Greater light-beam projection

Offering up to 30% more vision on the road, Philips VisionMoto headlamps are the perfect choice for motorcycle riders seeking light performance and safety. With better light output, riders can react faster to obstacles and avoid accidents.

Manufacturers' choice

For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

High-quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2650° C and glass 800° C) are able to withstand severe thermal shock. With the capability for increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.



Issue date 2018-07-03

Version: 10.0.1

12 NC: 8670 001 22266

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com