

PHILIPS

interior and
signaling bulb

BlueVision

Type of lamp: H6W

Pack of: 2

12 V,6 W

Style

12036BVB2



Drive with style

Ultimate brightness and unique stylish blue light

BlueVision signaling and interior bulbs are designed for drivers seeking to personalize their vehicles. With BlueVision signaling and interior lamps, drivers enjoy a blue xenon effect unmatched in a fully homologated road-legal lamp.

The best blue Xenon effect

- Xenon blue effect

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all applications
- Respecting high quality standards of the ECE homologation

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which application? Philips Automotive offering includes all car specific functions : license plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Xenon blue effect

Philips interior and signaling lamps are the best choice for driver seeking a stylish effect. The cool white light provides greater visibility in all car applications (License plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights).

Specifications

Electrical characteristics

Voltage: 12 V
Wattage: 6 W

Lifetime

Life time: 500h

Light characteristics

Lumens: 125 lm

Packaging Data

Packaging type: B2
EAN1: 8711500245670
EAN3: 8711500245687

Product description

Application: Interior, Rear position/ parking light, Reversing light
Base: BAX9s
Designation: H6W BlueVision ultra
Homologation ECE
Range: BlueVision
Technology: Conventional
Type: H6W

Outerpack information

Gross weight per piece: 0.198 kg
Height: 13 cm
Length: 15 cm
Width: 13.5 cm

Packed product information

Gross weight per piece: 9.9 g
Height: 12.9 cm
Length: 6.7 cm
Net weight per piece: 2.6 g
Width: 2.7 cm

Ordering information

Ordering code: 24567030
Order entry: 12036BVB2

