


Philips BlueVision  
Conventional Interior and  
Signaling

Type of lamp: H6W

Pack of: 10  
12 V,6 W

12036BVCP



## Drive with style

Ultimate brightness and unique stylish blue light

BlueVision signaling and interior bulbs are designed for drivers seeking to personalize their vehicles. With BlueVision signaling and interior lamps, drivers enjoy a blue xenon effect unmatched in a fully homologated road-legal lamp.

### **The best blue Xenon effect**

- Xenon blue effect

### **Original Equipment manufacturer**

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all applications
- Respecting high quality standards of the ECE homologation

# PHILIPS

# Specifications

## Electrical characteristics

- Voltage: 12 V
- Wattage: 6 W

## Lifetime

- Life time: Up to 500h

## Packaging Data

- Packaging type: CP
- EAN1: 8711500876096
- EAN3: 8727900370720

## Product description

- Application: Interior, Rear position/ parking light, Reversing light
- Base: BAX9s
- Designation: H6W BlueVision ultra
- Homologation ECE
- Range: BlueVision

- Technology: Conventional
- Type: H6W

## Outerpack information

- Gross weight per piece: 0.669 kg
- Height: 11.6 cm
- Length: 16.9 cm
- Width: 10.4 cm

## Packed product information

- Gross weight per piece: 3.345 g
- Net weight per piece: 2.6 g

## Ordering information

- Ordering code: 87609628

## Marketing specifications

- Expected benefits: More Vision


# Highlights

## Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## Designed for multiple usage



Which 12V lamp for which application? Philips Automotive offering includes all car specific functions : license plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights.

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Xenon blue effect

Philips interior and signaling lamps are the best choice for driver seeking a stylish effect. The cool white light provides greater visibility in all car applications (License plate lights, rear position/ parking light, glove box lights, interior signaling, front parking lights).



Issue date 2018-05-23

Version: 6.0.1

12 NC: 9230 458 17120  
EAN: 87 11500 87609 6

© 2018 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)