

# PHILIPS

Conventional Interior  
and Signalling

VisionPlus

Type of lamp: W5W

Pack of: 2

12 V, 21 W

12040VPB2



## Feel safe, drive safe

Superior quality with enhanced visibility

VisionPlus lamps produce more powerful light output compared to standard. VisionPlus is the performance choice for safety-conscious drivers. Offering high performance and excellent value, it is the right choice for demanding drivers.

### Increased visibility

- More powerful light output

### Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12 V lamps to meet all functions
- Complying with the high quality standards of ECE homologation

# Highlights

## Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## Designed for multiple usage



Which 12V lamp for which function? Philips Automotive offering includes all car specific functions: high beam, low beam, front fog, front

indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, licence plate lights, rear position/parking light, interior lights.

## ECE homologation

Philips automotive products and services are considered best in class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## More powerful light output

Brake lighting is visible earlier thanks to a more powerful light output. The following vehicle's braking distance can be reduced by up to 3 metres at 60 mph (100 km/h).

# Specifications

## Electrical characteristics

**Voltage:** 12 V

**Wattage:** 6 W

## Lifetime

**Life time:** Up to 1500 h

## Light characteristics

**Lumens:** 84 lm

## Packaging Data

**EAN3:** 8711559524184

**EAN1:** 8711559524160

**Packaging type:** B2

## Product description

**Application:** Interior

**Base:** W 2.1 x D 9.5

**Designation:** WBT10

**Homologation ECE:** NO

**Range:** VisionPlus

**Technology:** Conventional

**Type:** WB T10

## Outer pack information

**Gross weight per piece:** 0.195 kg

**Height:** 12 cm

**Length:** 14.5 cm

**Width:** 12 cm

## Packed product information

**Pack Quantity:** 2

**MOQ (for professionals):** 20

**Height:** 13.5 cm

**Length:** 0.95 cm

**Net weight per piece:** 1.13 g

**Width:** 9.5 cm

## Ordering information

**Ordering code:** 52416030

## Marketing specifications

**Expected benefits:** More light

