



Philips Standard
Conventional Interior and
Signaling

H27W/1
12V
27W

12059C1



Feel safe, drive safe

Philips standard lamps

Our headlight lamps are the choice of all major car manufacturers. They offer best in class quality at a competitive price.

Original equipment manufacturer

- Philips is the choice of major car manufacturers

Wide range of 12V lamps

- Wide range of 12V lamps to meet all applications

Quality standards according to ECE regulations

- Respecting high quality standards of the ECE homologation

Change in pairs

- Change both your headlamps at once for more safety

PHILIPS

Specifications

Electrical characteristics

- Voltage: 12 V
- Wattage: 27 W

Packaging Data

- EAN1: 8711559528540
- EAN3: 8727900370799
- Packaging type: C1

Product description

- Application: Front fog
- Homologation ECE
- Range: Standard
- Technology: Halogen
- Type: H27W/1
- Base: PG13
- Designation: 12059C1

Outerpack information

- Gross weight per piece: 0.183 kg

- Height: 7 cm
- Length: 18.5 cm
- Width: 7.5 cm

Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 10
- Gross weight per piece: 15.2 g
- Height: 6.5 cm
- Length: 3.5 cm
- Net weight per piece: 11.2 g
- Width: 3.5 cm

Ordering information

- Order entry: 12059C1
- Ordering code: 52854030

Marketing specifications

- Expected benefits: Standard
- Product highlight: Philips standard lamps

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

ECE homologation

We are dedicated to producing best-in-class Philips automotive products and services in the aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximize the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000).

Designed for multiple usage

Which 12V lamp for which application? Philips Automotive offering includes all car specific functions : license plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights.

Change in pairs

It is highly recommended to change them in pairs for symmetrical light performance.



Issue date 2016-12-20

Version: 4.0.1

12 NC: 9230 031 17102
EAN: 87 11559 52854 0

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com