

PHILIPS

Conventional Interior
and Signaling


Vision

Type of lamp: W21/5W

Pack of: 2

12 V, 21 W

12066B2



Feel safe, drive safe

Philips signaling lamps

Our Signalling lights are the choice of major car manufacturers. They offer best-in-class quality at a competitive price.

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all functions
- Respecting high quality standards of the ECE homologation




Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which function ? Philips Automotive offering includes all car specific functions : high beam, Low beam, front fog ,

front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Electrical characteristics

Voltage: 12 V
Wattage: 5, 21 W

Lifetime

Life time: Up to 400 h

Light characteristics

Lumens: 440 lm

Packaging Data

EAN3: 8727900697407
EAN1: 8727900697391
Packaging type: B2

Product description

Application: Rear position/ parking light, Stop light, Daytime running light, Tail light
Base: W3x16q
Designation: W21/5W, WY21W
Homologation ECE
Range: Vision
Technology: Conventional
Type: W21/5W

Outerpack information

Gross weight per piece: 0.307 kg
Length: 27.8 cm
Width: 13.5 cm

Packed product information

Pack Quantity: 2
MOQ (for professionals): 20
Gross weight per piece: 13, 15.3 g
Height: 12.9 cm
Length: 6.7 cm
Net weight per piece: 8 g
Width: 2.7 cm

Ordering information

Ordering code: 69739130

Marketing specifications

Expected benefits: More light

