

PHILIPS

Conventional Interior
and Signaling

Vision

Type of lamp: W16W

Pack of: 10

12 V,16 W

12067CP



Feel safe, drive safe

Philips signaling lamps

Our Signaling lamps are the choice of major car manufacturers. They offer best in class quality at competitive price.

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all functions
- Respecting high quality standards of the ECE homologation

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Designed for multiple usage



Which 12V lamp for which function ? Philips Automotive offering includes all car specific functions : high beam, Low beam, front fog ,

front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Electrical characteristics

Voltage: 12 V

Wattage: 16 W

Lifetime

Life time: Up to 700h

Light characteristics

Lumens: 310 lm

Packaging Data

EAN3: 8727900395594

EAN1: 8727900395556

Packaging type: CP

Product description

Application: Front indicator, Rear fog light, Rear indicator, Reversing light, Side indicator, Stop light, Tail light

Base: BAU15s

Designation: W16W

Homologation ECE

Range: Standard

Technology: Conventional

Type: W16W

Outerpack information

Gross weight per piece: 1.7 kg

Height: 13.1 cm

Length: 28.9 cm

Width: 18.8 cm

Packed product information

Pack Quantity: 1

MOQ (for professionals): 50

Gross weight per piece: 8.5 g

Net weight per piece: 1.95 g

Ordering information

Ordering code: 39555673

Marketing specifications

Expected benefits: Standard

