



Philips LongLife EcoVision  
Conventional Interior and  
Signaling

Type of lamp: PS19W

Pack of: 1  
12 V, 19 W

12085LLC1



## Drive with care

### Extended lifetime

Tired of changing your signaling and interior bulbs all the time? With extended lifetime LongLife, is the choice for drivers seeking to minimize maintenance on their vehicles.

#### Extended lifetime

- Extended lifetime for better value

#### Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Wide range of 12V lamps to meet all applications
- Respecting high quality standards of the ECE homologation

# PHILIPS

# Specifications

## Electrical characteristics

- Voltage: 12 V
- Wattage: 19 W

## Lifetime

- Life time: Up to 2300h

## Light characteristics

- Lumens: 350 lm

## Packaging Data

- EAN3: 8727900390926
- EAN1: 8727900700466
- Packaging type: C1

## Product description

- Application: Rear fog light, Rear position/ parking light, Reversing light, Daytime running light
- Base: PG20/1
- Designation: PS 19W LongLife
- Homologation ECE
- Range: LongLife EcoVision
- Technology: Conventional
- Type: PS19W

## Outerpack information

- Gross weight per piece: 0.25 kg
- Height: 12 cm
- Length: 14.5 cm
- Width: 12 cm

## Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 10
- Gross weight per piece: 16.667 g
- Height: 6.5 cm
- Length: 3.5 cm
- Net weight per piece: 9 g
- Width: 3.5 cm

## Ordering information

- Ordering code: 70046630
- Order entry: 12085LLC1

## Marketing specifications

- Expected benefits: Long lasting

12085LLC1

# Highlights

## Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## Designed for multiple usage



Which 12V lamp for which application? Philips Automotive offering includes all car specific functions : license plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights.

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Extended lifetime

LongLife signaling and interior lights are the best choice for drivers seeking optimal value. Their increased lifetime combined with high heat and vibration resistance guarantees a hassle free drive for extended periods of time.



Issue date 2019-08-21

Version: 7.0.1

12 NC: 9246 521 17104  
EAN: 87 27900 70046 6

© 2019 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)