

# PHILIPS


Headlight bulb

LongLife EcoVision

Type of lamp: H1

Pack of: 1

12 V,55 W



12258LLECOB1

## Drive with care

### Higher lifetime, less replacement

Tired of changing your headlight bulbs all the time? With higher lifetime of a car bulb, Philips LongLife EcoVision is the choice for drivers seeking to minimise maintenance on their vehicles.

#### **Lasts significantly longer than a standard lamp**

- No replacement necessary for 100 000 km
- High quality filament design to minimize maintenance
- Less waste thanks to fewer replacement
- Wide range of 12V lamps to meet all functions
- Change both your headlamps at once for more safety

#### **Original Equipment manufacturer**

- Philips are the choice of major car manufacturers.
- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation

#### **Very high quality and ultra resistant car lamp**

- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

# Highlights

## Change by pairs



Highly recommended to change them by pairs for symmetric light performance

## Designed for multiple usage



Which 12V lamp for which function ? Philips Automotive offering includes all car specific functions : high beam, Low beam, front fog , front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights.

## Drive several times longer

With Philips LongLife EcoVision drivers don't have to worry about changing a headlamp for at least 100 000 km.

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## High quality quartz glass




UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

## Reduced maintenance



With Philips LongLifeEcoVision you need significantly fewer lamp replacements. This makes them the ideal lamp for high voltage cars.

## Resistance against humidity



Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : if a drop of cold water

touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

## Award-winning car lamps



Our lamps are often rewarded by automotive experts

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

## Reduce waste, drive greener

It is the right choice for drivers looking for an environmentally friendly lighting solution.

## Car manufacturers' choice

For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

# Specifications

## Packaging Data

EAN3: 8727900361971  
EAN1: 8727900361964  
Packaging type: B1

## Electrical characteristics

Voltage: 12 V  
Wattage: 55 W

## Lifetime

Life time: 1250h

## Light characteristics

Lumens: 1550 ±15% lm  
Color temperature: Up to 3100 K

## Ordering information

Order entry: 12258LLECOB1  
Ordering code: 36196430

## Outerpack information

Gross weight per piece: 0.22 kg  
Height: 10.5 cm  
Length: 19.6 cm  
Width: 15.6 cm

## Product description

Type: H1  
Application: High beam, Front fog light, Low beam  
Designation: H1 LongLife EcoVision  
Homologation ECE

Range: LongLife EcoVision  
Technology: Halogen  
Base: P14,5s

## Packed product information

Pack Quantity: 1  
MOQ (for professionals): 10  
Gross weight per piece: 22 g  
Height: 13.5 cm  
Length: 2.5 cm  
Net weight per piece: 7 g  
Width: 9.5 cm

## Marketing specifications

Expected benefits: Long Life  
Product highlight: 1500 h

