

PHILIPS

car headlight bulb

LongLife EcoVision

Type of lamp: H1

Pack of: 2

12 V,55 W



12258LLECOS2



Drive with care

Higher lifetime, less replacement

Tired of changing your headlight bulbs all the time? With higher lifetime of a car bulb, Philips LongLife EcoVision is the choice for drivers seeking to minimise maintenance on their vehicles.

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation

Very high quality and ultra resistant car lamp

- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

Lasts significantly longer than a standard lamp

- Change both your headlamps at once for more safety
- Wide range of 12V lamps to meet all functions
- No replacement necessary for 100 000 km
- Less waste thanks to fewer replacement
- High quality filament design to minimize maintenance

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Change by pairs



Highly recommended to change them in pairs for symmetrical light performance.

Designed for multiple usage



Which 12V lamp for which function ? Philips Automotive offering includes all car specific functions : high beam, Low beam, front fog , front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights.

Drive several times longer

With Philips LongLife EcoVision drivers don't have to worry about changing a headlamp for at least 100 000 km.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

High quality quartz glass




UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Reduced maintenance



With Philips LongLifeEcoVision you need significantly fewer lamp replacements. This makes them the ideal lamp for high voltage cars.

Resistance against humidity



Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

Rewarded Car lamps



Our lights are often awarded by automotive experts.

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

Reduce waste, drive greener

It is the right choice for drivers looking for an environmentally friendly lighting solution.

Specifications

Packaging Data

EAN3: 8727900362565
EAN1: 8727900362558
Packaging type: S2

Electrical characteristics

Voltage: 12 V
Wattage: 55 W

Lifetime

Life time: Up to 1250 h

Light characteristics

Lumens: 1550 ±15% lm
Color temperature: Up to 3100 K

Ordering information

Order entry: 12258LLECOS2
Ordering code: 36255828

Outerpack information

Gross weight per piece: 0.46 kg
Height: 12 cm
Length: 28.6 cm
Width: 14.1 cm

Product description

Type: H1
Application: High beam, Front fog light, Low beam
Designation: H1 LongLife EcoVision
Homologation ECE

Range: LongLife EcoVision
Technology: Halogen
Base: P14,5s

Packed product information

Pack Quantity: 2
MOQ (for professionals): 10
Gross weight per piece: 46 g
Height: 13.3 cm
Length: 5.3 cm
Net weight per piece: 7 g
Width: 11 cm

Marketing specifications

Expected benefits: Long lasting
Product highlight: Lifetime up to 1500 hours

