



Philips VisionPlus
car headlight bulb

Type of lamp: H1

Pack of: 1
12 V, 55 W



12258VPB1

Feel safe, drive safe

Up to 60% more vision: fast reactions save lives

Philips VisionPlus headlight bulbs produce 60% more vision, which allows drivers to see farther for greater safety and comfort. Offering high performance and excellent value, VisionPlus is the right choice for today's demanding drivers.

Superior quality with enhanced visibility

- VisionPlus projects 25 m light extra than a standard lamp
- Greater driving comfort and safety
- Wide range of 12V lamps to meet all functions
- Change both your headlamps at once for more safety

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation

Very high quality and ultra resistant car lamp

- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

PHILIPS

car headlight bulb
Type of lamp: H1 Pack of: 1, 12 V,55 W

12258VPB1

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Change by pairs



Highly recommended to change them by pairs for symmetric light performance

Designed for multiple usage



Which 12V lamp for which function ? Philips Automotive offering includes all car specific functions : high beam, Low beam, front fog, front indicator, side indicator, rear indicator,

stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

High quality and visibility




VisionPlus provides you with a better reactivity thanks to an earlier recognition of obstacles and traffic signs. Brake lighting is also visible earlier, thanks to a more powerful light output. Drivers can reduce their braking distance by up to 3 meters at 100 km/h. Light is a fundamental part of the driving experience and light is the first and only part of the safety circle that actually helps prevent accidents.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Resistance against humidity



Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

Rewarded Car lamps



Our lamps are often rewarded by automotive experts

car headlight bulb
Type of lamp: H1 Pack of: 1, 12 V,55 W

12258VPB1

Specifications

Packaging Data

- EAN3: 8727900363197
- EAN1: 8727900363203
- Packaging type: B1

Electrical characteristics

- Voltage: 12 V
- Wattage: 55 W

Lifetime

- Life time: 350h

Light characteristics

- Lumens: 1780 max. lm
- Color temperature: Up to 3250 K

Ordering information

- Order entry: 12258VPB1
- Ordering code: 36320330

Outerpack information

- Gross weight per piece: 0.259 kg
- Height: 11 cm

- Length: 19.5 cm
- Width: 15.3 cm

Product description

- Type: H1
- Application: High beam, Front fog light, Low beam
- Designation: H1 VisionPlus
- Homologation ECE
- Range: VisionPlus
- Technology: Halogen
- Base: P14,5s

Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 10
- Gross weight per piece: 25.9 g
- Height: 13.5 cm
- Length: 2.568 cm
- Net weight per piece: 5.95 g
- Width: 9.5 cm

Marketing specifications

- Expected benefits: More light
- Product highlight: Up to 60% more vision



Issue date 2020-02-04

Version: 8.0.1

12 NC: 9240 220 17181
EAN: 87 11500 40631 6

© 2020 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com