



Philips X-tremeVision  
Headlight bulb

Type of lamp: H1

Pack of: 2+2  
12 V,55 W



12258XVSM

## Feel safe, drive safe

Boosts your vision on the road

Philips X-tremeVision halogen headlamp offers up to 100% more vision. X-tremeVision is engineered with state-of-the-art technology for ultimate bright light. It is ECE compliant for road legal use.

### 100% more light for maximum visibility\*

- See further and react faster with up to 100% more vision

### Enhancing safety with increased visibility

- Greater driving comfort and safety

### Fully homologated, road-legal bright light

- Complying with high quality standards of ECE homologation

### High quality and ultra resistant headlamp

- Philips is the choice of major car manufacturers
- Change both your headlamps simultaneously for more safety
- Award-winning car lamp manufacturer
- Philips car lamps are made of high-quality quartz glass<sup>^</sup>
- Philips car lamps are highly resistant against humidity<sup>^</sup>
- Philips car lamps are highly UV resistant
- Wide range of 12V lamps for all functions

# PHILIPS

Headlight bulb  
Type of lamp: H1 Pack of: 2+2, 12 V,55 W

12258XVSM

# Highlights

## 100% more vision on the road

Based on the unique product design, X-tremeVision is offering ultimate bright light on the road

## High quality and visibility

X-tremeVision gives you faster reaction time thanks to an earlier recognition of obstacles and traffic signs. Light is a fundamental part of the driving experience and light is key in preventing accidents. This product actively prevents accidents by increasing overall visibility and road illumination.

## ECE homologation

X-tremeVision is fully compliant to ECE for road-legal use.

## Designed for multiple usage



Which 12V lamp for which function? Philips Automotive offers all car specific functions : high beam, Low beam, front fog, front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, license plate lights, rear position/parking light, interior lights

## Change by pairs



Highly recommended to change them by pairs for symmetric light performance

## Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

## Commended Car lamps




Our lamps are often commended by automotive experts.

## High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, eliminating the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability to withstand increased pressure inside the lamp, UV-quartz glass is able to produce more powerful lighting. ^Application varies per bulb type.

## Resistance against humidity



Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit. ^Application varies per bulb type

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass ideal for all driving conditions and ensures their longevity at the same time.

Headlight bulb  
Type of lamp: H1 Pack of: 2+2, 12 V,55 W

12258XVSM

# Specifications

## Packaging Data

- Packaging type: SM
- EAN1: 8727900368352
- EAN3: 8727900368666

## Electrical characteristics

- Voltage: 12 V
- Wattage: 55 W

## Lifetime

- Life time: 0

## Light characteristics

- Lumens: 1550  $\pm$ 15% lm

## Ordering information

- Order entry: 12258XVS2
- Ordering code: 78898630

## Outerpack information

- Gross weight per piece: 0.362 kg
- Height: 14 cm
- Length: 29.6 cm
- Width: 11.6 cm

## Product description

- Type: H1
- Application: High beam, Front fog light, Low beam
- Designation: H1 X-tremeVision
- Homologation ECE
- Marking ECE: E1 21P
- Range: X-tremeVision
- Technology: Halogen
- Base: P14,5s

## Packed product information

- Gross weight per piece: 36.2 g
- Height: 12.62 cm
- Length: 10.6 cm
- Net weight per piece: 5.95 g
- Pack Quantity / MOQ: 20
- Width: 5.6 cm

## Marketing specifications

- Expected benefits: More light
- Product highlight: 100% more vision



Issue date 2018-08-10

Version: 7.0.2

12 NC: 8670 001 00706

© 2018 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)