



Philips Standard  
Conventional Interior and  
Signalling

Type of lamp: PSX24W

Pack of: 1  
12 V, 24 W

12276C1



## Feel safe, drive safe

### Philips standard bulbs

Our Signaling lamps are the choice of major car manufacturers. They offer best in class quality at competitive price.

#### **Original equipment manufacturer**

- Philips is the choice of major car manufacturers

#### **Wide range of 12-V bulbs**

- Wide range of 12-V lamps to meet all applications

#### **Quality standards according to ECE regulations**

- Complying with the high quality standards of ECE homologation

#### **Change in pairs**

- Change both your headlamps at once for more safety

# PHILIPS

# Specifications

## Electrical characteristics

- Voltage: 12 V
- Wattage: 24 W

## Packaging Data

- EAN1: 8727900696769
- EAN3: 8727900390902
- Packaging type: C1

## Product description

- Application: Front fog
- Homologation ECE
- Range: Standard
- Technology: Halogen
- Type: PSX24W
- Base: PG20/7
- Designation: 12276C1

## Outer pack information

- Gross weight per piece: 0.171 kg

- Height: 7 cm
- Length: 18.5 cm
- Width: 7.5 cm

## Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 10
- Gross weight per piece: 14 g
- Height: 6.5 cm
- Length: 3.5 cm
- Net weight per piece: 10 g
- Width: 3.5 cm

## Ordering information

- Order entry: 12276C1
- Ordering code: 69676930

## Marketing specifications

- Expected benefits: Standard
- Product highlight: Philips standard bulbs

12276C1

# Highlights

## Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## ECE homologation

We are dedicated to producing best-in-class Philips automotive products and services in the aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximise the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000).

## Designed for multiple usage

Which 12-V lamp for which application? Philips' Automotive offering includes all car-specific functions: numberplate lights, rear position/parking light, glove box lights, interior signalling, front parking lights.

## Change in pairs

It is highly recommended that you change them in pairs for symmetrical light performance.



Issue date 2018-07-03

Version: 7.0.1

12 NC: 9246 527 17104  
EAN: 87 27900 69676 9

© 2018 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)