



Philips Standard
Conventional Interior and
Signalling

Type of lamp: P13W

Pack of: 1
12 V, 13 W

12277C1



Feel safe, drive safe

Philips standard bulbs

Our Signalling lights are the choice of major car manufacturers. They offer best-in-class quality at a competitive price.

Original equipment manufacturer

- Philips is the choice of major car manufacturers

Wide range of 12-V bulbs

- Wide range of 12-V lamps to meet all applications

Quality standards according to ECE regulations

- Complying with the high quality standards of ECE homologation

Change in pairs

- Change both your headlamps at once for more safety

PHILIPS

Specifications

Electrical characteristics

- Voltage: 12 V
- Wattage: 13 W

Packaging Data

- EAN1: 8727900696721
- EAN3: 8727900391008
- Packaging type: C1

Product description

- Application: Daytime running light
- Base: PG18.5d-1
- Homologation ECE
- Range: Vision, Standard
- Technology: Halogen
- Type: P13W
- Designation: 12277C1

Outer pack information

- Gross weight per piece: 0.161 kg

- Height: 7 cm
- Length: 18.5 cm
- Width: 7.5 cm

Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 10
- Height: 6.5 cm
- Length: 3.5 cm
- Width: 3.5 cm
- Gross weight per piece: 8 g
- Net weight per piece: 3.5 g

Ordering information

- Order entry: 12277C1
- Ordering code: 69672130

Marketing specifications

- Expected benefits: Standard
- Product highlight: Philips standard bulbs

12277C1

Highlights

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

ECE homologation

We are dedicated to producing best-in-class Philips automotive products and services in the aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximise the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000).

Designed for multiple usage

Which 12-V lamp for which application? Philips' Automotive offering includes all car-specific functions: numberplate lights, rear position/parking light, glove box lights, interior signalling, front parking lights.

Change in pairs

It is highly recommended that you change them in pairs for symmetrical light performance.



Issue date 2019-09-20

Version: 9.0.1

12 NC: 9246 528 17104
EAN: 87 27900 69672 1

© 2019 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com