

PHILIPS

Headlight bulb

BlueVision ultra

Type of lamp: H4

Pack of: 2+2

12 V,60/55 W



12342BVUSM



Drive with style

Ultimate brightness and unique stylish blue light

BlueVision ultra headlights are for drivers seeking to personalize their vehicles. With BlueVision ultra, drivers enjoy a blue xenon effect thanks to its unique Gradient Coating™ technology, unmatched in a fully homologated road-legal lamp.

The best blue Xenon effect for halogen lamps

- 3 700K bright white light on the road
- BlueVision ultra is based on a Gradient Coating™ technology
- 2 signaling W5W are offered with BlueVision ultra
- Change both your headlamps at once for more safety

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation

Very high quality and ultra resistant car lamp

- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

Highlights

2 signaling W5W offered



Give your car a full stylish blue look thanks to the 2 blue W5W offered

3 700 K bright white light

With a white light of 3 700 K, BlueVision Moto lamps offer a greater visibility on the road and a unique effect in the optics which makes you stand out amongst other riders.

A unique coating technology



Thanks its exclusive Gradient Coating™ technology, BlueVision ultra further improves the xenon effect in the headlight.

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern

automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Change by pairs



Highly recommended to change them by pairs for symmetric light performance

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.


High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the

capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Resistance against humidity



Only a burning bulb made of quartz glass (filament 2650°C, glass 800°C) can resist thermal shocks : if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

Rewarded Car lamps



Our lamps are often rewarded by automotive experts

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

Specifications

Packaging Data

Packaging type: SM
EAN1: 8727900350340
EAN3: 8727900350357

Electrical characteristics

Voltage: 12 V
Wattage: 60/55 W

Lifetime

Life time: 400h

Light characteristics

Color temperature: 4000 K
Lumens: 1650 lm

Ordering information

Order entry: 12342BVUSM
Ordering code: 35034028

Outerpack information

Gross weight per piece: 0.58 kg
Height: 12 cm
Length: 28.6 cm
Width: 14.1 cm

Product description

Type: H4
Application: High beam, Front fog light, Low beam
Designation: H4 BlueVision ultra
Homologation ECE

Range: BlueVision Ultra
Technology: Halogen
Base: P43t-38

Packed product information

Gross weight per piece: 116 g
Height: 13.3 cm
Length: 5.3 cm
Net weight per piece: 22.63 g
Pack Quantity / MOQ: 5
Width: 11 cm

Marketing specifications

Expected benefits: Style
Product highlight: Xenon ultimate effect

