

PHILIPS

Preliminary

car headlight bulb

CrystalVision

H4

12V

60W/55W

2x T10 LED lamps included

12342CVSL



Drive with style

Bright white light

Philips CrystalVision halogen headlamp upgrades the style of your car with 4300K bright white light. With the blue coating and the silver top finishing, your car will look more stylish

Bright white light up to 4300K


- CrystalVision 4300K bright white light for style upgrade
- Bright white color match effect for high end look

High quality and ultra resistant headlamp

- Philips car lamps are made of high-quality quartz glass[^]
- Philips car lamps are highly resistant against humidity[^]
- Philips car lamps are highly UV resistant
- Change both your headlamps simultaneously for more safety
- Philips is the choice of major car manufacturers.

Highlights

4300K bright white light



With the blue coating and silver top design, CrystalVision is offering bright white headlight of 4300K to see and to be seen, for both city and country driving

High-end look car

Supplied with two colour matching T10 LED position lamps, CrystalVision gives your car lights the premium look of high end cars.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, eliminating the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability to withhold increased pressure inside the lamp, UV-quartz glass is able to produce more powerful lighting. ^Application varies per bulb type.

Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°C, glass 800°C) can resist thermal shocks : such as, if a drop of cold water

touches the hot bulb, when you drive through water with a broken headlight unit.

^Application varies per bulb type

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

Change by pairs



Highly recommended to change them by pairs for symmetric light performance

Car manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standards on modern automobiles. Today, one in two cars in Europe and one in three worldwide, is equipped with Philips lighting.

Specifications

Product description

Technology: Halogen
Application: Additional high beam, High beam, Low beam
Designation: H4 CrystalVision
Homologation ECE: NO
Range: CrystalVision
Type: H4
Base: P43t-38

Electrical characteristics

Voltage: 12 V
Wattage: 60 W/55 W

Lifetime

Life time: B3/Tc = 300/500

Light characteristics

Color temperature: up to 4300 K
Lumens [lm]: 1100m ± 15%

Packaging Data

EAN1: 8727900354393
EAN3: 8727900354409
Packaging type: SL

Ordering information

Order entry: 12342CVSL
Ordering code: 35439330

Marketing specifications

Expected benefits: Bright white light
Product highlight: 4300K

Outerpack information

Gross weight per piece: 2.89 kg
Height: 12.6 cm
Length: 27.6 cm
Width: 22.8 cm

Packed product information

Gross weight per piece: 144.5 g
Height: 10.9 cm
Length: 10.9 cm
Net weight per piece: 21.5 g
Pack Quantity / MOQ: 20
Width: 5.3 cm

