



Philips CrystalVision ultra  
Motorcycle headlights

Type of lamp: H4

Pack of: 1  
12V, 60/55W  
More style



12342CVUBW

## Ride with style

Bright white light

Philips CrystalVision ultra moto halogen headlamp upgrades the style of your motorcycle with a bright white light.

### White modern xenon look

- Bright white light for a stylish xenon look

### High-quality and ultra-resistant headlamp

- Philips moto lamps are made of high-quality quartz glass
- Respecting the high quality standards of ECE homologation
- The favoured choice of major motorcycle manufacturers

# PHILIPS

Motorcycle headlights  
Type of lamp: H4 Pack of: 1, 12V, 60/55W, More style

# Specifications

## Marketing specifications

- Expected benefits: More style

## Product description

- Application: High beam, Low beam
- Base: P43t-38
- Designation: 12342CVUBW
- ECE certification
- Range: CrystalVision ultra Moto
- Technology: Halogen
- Type: H4

## Light characteristics

- Colour temperature: Up to 3700 K

## Electrical characteristics

- Wattage: 60/55 W
- Voltage: 12 V

## Ordering information

- Order entry: 12342CVUBW
- Ordering code: 22148330

## Packaging Data

- EAN1: 8711500221483
- EAN3: 8711500221490
- Packaging type: BW

## Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 10
- Length [cm]: 9.5
- Width [cm]: 4.9
- Height [cm]: 12.9
- Net weight per piece [g]: 21.2
- Gross weight per piece [g]: 33.6

## Outer pack information

- Length [cm]: 25.5
- Width [cm]: 19
- Height [cm]: 13
- Gross weight per piece [kg]: 0.462

12342CVUBW

# Highlights

## White light for motorcycle

CrystalVision ultra moto is a unique halogen lamp that offers a bright white light. High-tech and efficient to differentiate and personalise your motorcycle, with better visibility and comfort.

## High-quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. So Philips quartz-glass lamps (filament 2 650°C and glass 800°C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light. And more powerful light means an enhanced driving experience, however dark the road in front of you.

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality materials and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Manufacturers' choice

For over 100 years, Philips bulbs have been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard in modern vehicles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.



Issue date 2024-01-18

Version: 8.1.1

© 2024 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)