

Preliminary

Philips CrystalVision ultra  
Motorcycle headlights

Type of lamp: H4

Pack of: 1  
12V, 60/55W  
More style

12342CVUBW



## Ride with style

Bright white light

Philips CrystalVision ultra moto halogen headlamp upgrades the style of your motorcycle with a bright white light.

### **White modern xenon look**

- Bright white light for a stylish xenon look

### **High quality and ultra-resistant headlamp**

- Philips moto lamps are made of high-quality quartz glass
- Respecting high quality standards of the ECE homologation
- The favored choice of major motorcycle manufacturers

**PHILIPS**

## Especificaciones

### Packaging Data

- Packaging type: BW
- EAN1: 8711500221483
- EAN3: 8711500221490

### Light characteristics

- Color temperature: 3700K

### Marketing specifications

- Expected benefits: More style

### Product description

- Range: CrystalVision ultra Moto
- Technology: Halogen
- Application: High beam, Low beam
- Type: H4
- Homologation ECE: YES
- Designation: 12342CVUBW
- Base: P43t-38

### Electrical characteristics

- Voltage: 12 V
- Wattage: 35/35 W

### Ordering information

- Order entry: 12342CVUBW
- Ordering code: 22148330

### Packed product information

- Gross weight per piece [g]: 33.6
- Height [cm]: 12.9
- Length [cm]: 9.5
- MOQ (for professionals): 10
- Net weight per piece [g]: 21.2
- Pack Quantity: 1
- Width [cm]: 4.9

### Outerpack information

- Gross weight per piece [kg]: 0.462
- Height [cm]: 13
- Length [cm]: 25.5
- Width [cm]: 19

## Destacados

### White light for motorcycle

CrystalVision ultra moto is a unique halogen lamp, that offers a bright white light. High technology and efficiency to differentiate and personalize your motorcycle, with better visibility and confort.

### High quality quartz glass

UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. So Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light. And more powerful light means an enhanced driving experience, however dark the road in front of you.

### ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality materials and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

### Manufacturers' choice

For over 100 years, Philips lamps have been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard in modern vehicles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

