

# PHILIPS


car headlight bulb

RacingVision

Type of lamp: H4

Pack of: 1

12 V,60/55 W



12342RVB1



## Maybe the strongest legal halogen lamp ever built

Take your lights and your driving to the limit

Philips RacingVision car bulbs are the perfect choice for passionate drivers. With an incredible performance of up to 150% more brightness, you'll be able to react faster for a safer, more exciting driving experience.

### Increased performance for more fun

- See further and react faster with up to 150% more brightness
- One of the brightest bulbs for excellent light performance

### The road-legal rallye bulb

- Brighter light for sportive drivers
- Brighter lights mean no surprises and enhanced control
- Improved light contrast for a safer, more exciting drive
- Respecting high quality standards of the ECE homologation

### Optimized for winter light conditions

- Strong road-legal headlights for darker conditions

# Highlights

## See further, react faster

When driving at night you need the very best visibility. The further you can see clearly, the faster you can react to whatever appears on the road. Philips RacingVision headlamps boost your visibility with up to 150% more brightness. You'll recognize obstacles in your way earlier than with other less powerful halogen lamps. So you get to enjoy a safer, more pleasant journey.

## Excellent light performance

With better, brighter lights you're able to perform better on the road. With its optimized high-precision filament geometry, up to 13 bar high pressure gas filling, high precision chrome coating and high quality UV-Quartz glass, Philips RacingVision headlights set a new standard in automotive lighting. Engineered for performance and visibility, these headlights allow for a more relaxed, controlled and fun driving experience.

## Rally performance for the road

Sportive drivers expect more performance from their cars. Bringing up to 150% more brightness on the road, Philips RacingVision are homologated to provide you with fun experience offroad and on the road.

## Strong light, early reaction

When driving at higher speeds on poorly lit country roads, you rely on the performance of your headlights. Faced with an unexpected danger, reaction time is everything. Even split seconds can make a crucial difference to your safety. The superior beam performance of the Philips RacingVision headlamp helps you identify dangerous situations faster and stay in perfect control of your vehicle – whatever road conditions you're facing.

## Great contrast drives fun

Visual skills are pushed to the limit when driving at night. During low light conditions, or when experiencing glare from other vehicles, your ability to contrast between objects is significantly reduced. This makes it harder to spot obstacles, such as a pedestrian on the road. The specific color temperature in Philips RacingVision headlights (available in H4 and H7) allows your eyes to focus better and perceive contrasts in the distance. That makes you a safer road user. And with your limits increased, driving after dark is now a more exciting experience.

## ECE homologation

We produce best-in-class Philips products in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Bright light for darker months

Driving in winter is a challenge. But passionate drivers like to be tested. During those harsh winter months, you need to know your headlights are up to the job. Just as you would adapt to wintery roads by choosing winter tires, so you should demand the best visibility when driving in these darker, more dangerous conditions. Philips RacingVision headlamps give you more control in the toughest conditions, so you can worry less about the road and enjoy every ride.

# Specifications

## Product description

**Technology:** Halogen

**Type:** H4

**Range:** RacingVision

**Application:** High beam, Low beam

**Homologation ECE**

**Designation:** H4 RacingVision

**Base:** P43t-38

## Electrical characteristics

**Voltage:** 12 V

**Wattage:** 55 W

## Light characteristics

**Lumens:** 1650 lm

**Color temperature:** Up to 3500 K

## Lifetime

**Life time:** 200 hrs

## Ordering information

**Order entry:** 12342RVB1

**Ordering code:** 00022430

## Packaging Data

**EAN1:** 8719018000224

**EAN3:** 8719018000231

**Packaging type:** B1

## Packed product information

**Gross weight per piece:** 5.2 g

**Height:** 12.9 cm

**Length:** 9.5 cm

**Width:** 4.86 cm

**MOQ (for professionals):** 10

**Pack Quantity:** 1

## Outerpack information

**Height:** 13 cm

**Length:** 25.5 cm

**Width:** 19 cm

**Gross weight per piece:** 0.625 kg

## Marketing specifications

**Expected benefits:** Style

**Product highlight:** Enjoy your passion

