

PHILIPS


car headlight bulb

RacingVision

Type of lamp: H4

Pack of: 1

12 V, 60/55 W



12342RVB1



Maybe the strongest legal halogen bulb ever built

Take your lights and your driving to the limit

Philips RacingVision car bulbs are the perfect choice for passionate drivers. With an incredible performance of up to 150% more brightness, you'll be able to react faster for a safer, more exciting driving experience.

Increased performance for more fun

- See further and react faster with up to 150% more brightness
- One of the brightest bulbs for excellent light performance

The road-legal rally bulb

- Brighter light for sporting drivers
- Brighter lights mean no surprises and enhanced control
- Improved light contrast for a safer, more exciting drive
- Respecting the high quality standards of ECE homologation

Optimised for winter light conditions

- Strong road-legal headlights for darker conditions

Highlights

See further, react faster

When driving at night you need the very best visibility. The further you can see clearly, the faster you can react to whatever appears on the road. Philips RacingVision headlamps boost your visibility with up to 150% more brightness. You'll recognise obstacles in your way earlier than with other, less powerful halogen bulbs. So you get to enjoy a safer, more pleasant journey.

Excellent light performance

With better, brighter lights you're able to perform better on the road. With their optimised high-precision filament geometry, up to 13-bar high-pressure gas filling, high-precision chrome coating and high-quality UV-Quartz glass, Philips RacingVision headlamps set a new standard in automotive lighting. Engineered for performance and visibility, these headlamps allow for a more relaxed, controlled and fun driving experience.

Rally performance for the road

Sporting drivers expect more performance from their cars. Bringing up to 150% more brightness on the road, Philips RacingVision bulbs are homologated to provide you with a fun experience both on the road and off-road.

Strong light, early reaction

When driving at higher speeds on poorly lit country roads, you rely on the performance of your headlights. When you're faced with an unexpected danger, reaction time is everything. Even split seconds can make a crucial difference to your safety. The superior beam performance of the Philips RacingVision headlamp helps you identify dangerous situations faster and stay in perfect control of your vehicle – whatever road conditions you're facing.

Great contrast drives fun

Visual skills are pushed to the limit when you are driving at night. In low-light conditions, or when you are experiencing glare from other vehicles, your ability to contrast between objects is significantly reduced. This makes it harder to spot obstacles, such as a pedestrian on the road. The specific colour temperature in Philips RacingVision headlamps (available in H4 and H7) allows your eyes to focus better and perceive contrasts in the distance. That makes you a safer road user. And with your limits increased, driving after dark is now a more exciting experience.

ECE homologation

We produce best-in-class Philips products in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Bright light for darker months

Driving in winter is a challenge. But passionate drivers like to be tested. During those harsh winter months, you need to know your headlights are up to the job. Just as you would adapt to wintery roads by choosing winter tyres, so you should demand the best visibility when driving in these darker, more dangerous conditions. Philips RacingVision headlamps give you more control in the toughest conditions, so you can worry less about the road and enjoy every ride.

Specifications

Product description

Technology: Halogen

Type: H4

Range: RacingVision

Application: High beam, Low beam

Homologation ECE

Designation: H4 RacingVision

Base: P43t-38

Electrical characteristics

Voltage: 12 V

Wattage: 55 W

Light characteristics

Lumens: 1650 lm

Colour temperature: Up to 3500 K

Lifetime

Life time: 200 hrs

Ordering information

Order entry: 12342RVB1

Ordering code: 00022430

Packaging Data

EAN1: 8719018000224

EAN3: 8719018000231

Packaging type: B1

Packed product information

Gross weight per piece: 5.2 g

Height: 12.9 cm

Length: 9.5 cm

Width: 4.86 cm

MOQ (for professionals): 10

Pack Quantity: 1

Outer pack information

Height: 13 cm

Length: 25.5 cm

Width: 19 cm

Gross weight per piece: 0.625 kg

Marketing specifications

Expected benefits: Style

Product highlight: Enjoy your passion

