



Philips VisionPlus
car headlight bulb

Type of lamp: H4

Pack of: 1
12 V, 60/55 W



12342VPB1

Feel safe, drive safe

Up to 60% more vision: fast reactions save lives

Philips VisionPlus headlight bulbs produce 60% more vision, which allows drivers to see farther for greater safety and comfort. Offering high performance and excellent value, VisionPlus is the right choice for today's demanding drivers.

Superior quality with enhanced visibility

- VisionPlus projects longer light beams than a standard lamp
- Greater driving comfort and safety
- Wide range of 12 V lamps to meet all functions
- Change both your headlamps at once for more safety

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Award-winning car lamp manufacturer
- Respecting the high-quality standards of the ECE homologation

Very high-quality and ultra-resistant car lamp

- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant to humidity
- Philips car lamps are highly UV resistant

PHILIPS

car headlight bulb
Type of lamp: H4 Pack of: 1, 12 V, 60/55 W

12342VPB1

Highlights

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

Change in pairs



It is highly recommended to change them in pairs for symmetrical light performance

Designed for multiple usage



Which 12V lamp for which function? Philips Automotive offering includes all car specific

functions: high beam, low beam, front fog, front indicator, side indicator, rear indicator, stop light, reversing light, rear fog light, licence plate lights, rear position/parking light, interior lights.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

High quality and visibility




VisionPlus provides you with a better reactivity thanks to an earlier recognition of obstacles and traffic signs. Brake lighting is also visible earlier, thanks to a more powerful light output. Drivers can reduce their braking distance by up to 3 metres at 100 km/h. Light is a fundamental part of the driving experience and light is the first and only part of the safety circle that actually helps prevent accidents.

High-quality quartz glass



UV-quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650°C and glass 800°C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Resistance to humidity



Only a burning bulb made of quartz glass (filament 2650°C, glass 800°C) can resist thermal shocks: if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

Award-winning car lamps



Our lamps are often rewarded by automotive experts

car headlight bulb
Type of lamp: H4 Pack of: 1, 12 V, 60/55 W

12342VPB1

Specifications

Packaging Data

- EAN3: 8727900399332
- EAN1: 8727900399349
- Packaging type: B1

Electrical characteristics

- Voltage: 12 V
- Wattage: 60/55 W

Lifetime

- Life time: 400h

Light characteristics

- Lumens: 1650 lm

Ordering information

- Order entry: 12342VPB1
- Ordering code: 39934930

Outer pack information

- Gross weight per piece: 0.42 kg
- Height: 14.1 cm
- Length: 26 cm
- Width: 14.5 cm

Product description

- Type: H4
- Application: High beam, Front fog light, Low beam
- Designation: H4 VisionPlus
- Homologation ECE
- Range: VisionPlus
- Technology: Halogen
- Base: P43t-38

Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 10
- Gross weight per piece: 42 g
- Height: 13.5 cm
- Length: 4.748 cm
- Net weight per piece: 21.5 g
- Width: 9.5 cm

Marketing specifications

- Expected benefits: More light
- Product highlight: Up to 60% more vision



Issue date 2017-07-12

Version: 7.0.1

12 NC: 9282 051 17110
EAN: 87 11500 40627 9

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com